



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 63

Connector Product Type: Housing

Operating Voltage: 250 VDC

Connector System: Wire-to-Panel

Sealable: No

Features

Dimensions

Compatible Insulation Diameter Range	1.73 mm[.068 in]
--------------------------------------	------------------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Thread Size	1-3/8 - 18 UNEF-2A
Panel Mount Feature Type	Flange with Mounting Holes
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Housing Features



Body Orientation	Straight
Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	23

Configuration Features

Reverse Numbering	Without
Number of Positions	63
Number of Power Positions	0
Number of Signal Positions	63

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Pin
Contact Current Rating (Max)	7.5 A
Contact Protection	With

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------



Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 207774-3
CLAMP CABLE SHELL,SIZE 23



TE Part # 207299-4
FLANGE PLUG



TE Part # 796382-2
R/A STRN RELIEF KIT,SZ 23,CPC




TE Part # 6-2407269-3
CAP, CPC, SIZE 23 RECP, RED



 TE Part # 6-2407269-4 CAP, CPC, SIZE 23 RECP, YELLOW	 TE Part # 206512-6 LARGE CABLE CLAMP KIT,BULK PKG	 TE Part # 206138-8 CLAMP CBL SHELL SIZE 23	 TE Part # 1-206138-0 CABLE CLAMP ASSY,BULK PACKED
 TE Part # 1546350-2 R/A CABLE CLAMP KIT,SZ 23,CPC	 TE Part # 206512-5 CLAMP,CABLE SHELL,SIZE 23	 TE Part # 207055-1 EXTENDER BACK SHELL	 TE Part # 6-2407269-2 CAP, CPC, SIZE 23 RECP, BLACK
 TE Part # 205842-1 CPC PLUG ASSEMBLY SIZE 23-63	 TE Part # 213812-1 COUPLING RING,SZ 23,CPC	 TE Part # 6-2407269-1 CAP, CPC, SIZE 23 RECP, ORANGE	 TE Part # 207774-4 CABLE CLAMP ASY,SZ 23,BULK PKG


Also in the Series | AMP CPC

 Circular Connector Backshells & Clamps(1)	 Circular Power Connectors(423)	 Connector Contacts(6)	 Connector Hardware(12)
 Power Contacts(6)	 Sealing Sleeves(2)		


Customers Also Bought



TE Part #1-1625963-5
HSA5 1R0 5%



TE Part #1415076-1
PT5S7LC4



TE Part #1-1761608-6
IDC LOW PRO HDR 60P VERT SHT
LAT BLK



TE Part #2-2176414-6
7W STD M/OX 5% 220R



TE Part #2-1623927-8
CFR16 5% 1K5




TE Part #2-1622796-6
YR1 0.1% 42K2



TE Part #5672696010
TSAS-NR502-X-10MM



TE Part #206151-3
CPC RECPT SEALED SIZE 23-37



TE Part #5-2287923-3
FAKRA, 2 POS, EXT-EDGE, ASS'Y 12
O'CLOCK



TE Part #2176384-6
RQ 1206 121R 0.1% 10PPM 1K RL

Documents

Product Drawings

CPC RECPT ASSEMBLY SIZE 23-63

English

CAD Files

Customer View Model

ENG_CVM_205843-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_205843-1_F.3d_stp.zip

English

Customer View Model

ENG_CVM_205843-1_F.2d_dxf.zip

English

3D PDF

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_205843-1_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205843-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_205843-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

Product Specifications

[Connector, Circular Plastic](#)

English

[Product Specification](#)

English

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English