



Relays & Contactors > Relay Accessories



Relay Socket Type: DIN Rail Mount
Body Material: Polycarbonate
Product Mount Type: DIN Rail
Pole Configuration: 2
Relay Accessory Type: DIN Rail Socket, Socket

Features

Mechanical Attachment

Product Mounting Feature Type	Snap-On
Product Mount Type	DIN Rail

Contact Features

Relay Socket Type	DIN Rail Mount
Pole Configuration	2

Body Features

Body Material	Polycarbonate
---------------	---------------

Product Type Features

Relay Accessory Type	DIN Rail Socket, Socket
----------------------	-------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-1419111-0
PT270615

TE Part # 9-1415001-1
PT270L24

TE Part # 1415002-1
PT270R24

TE Part # 4-1419111-8
PT270524

TE Part # 5-1419111-3
PT271024

TE Part # 5-1419111-6
PT271524

TE Part # 2-1415039-1
PT270S15

TE Part # 2071566-9
PT28D01





TE Part # 5-1419111-8
PT271730



TE Part # 4-1419111-2
PT270024



TE Part # 3-1415002-1
PT270T30



TE Part # 4-1419135-0
PT271615




TE Part # 5-1419111-1
PT270730




TE Part # 2071566-7
PT28D00

Also in the Series | **SCHRACK Accessories Miniature Relay PT**



Relay Accessories(52)

Customers Also Bought



TE Part #CAT-D9934-A78
Contact: Component To Wire; 22-24A,
16-10 wire size



TE Part #66361-3
III+ PIN,18-14,15AU/FL,LP



TE Part #66255-2
MALE CONTACT ASSY. (STRIP)



TE Part #5-104505-4
MTE PIN 22-26 AWG PLTD



TE Part #160018-2
RING TONGUE 176 20-16 AWG 0.251
NIBR



TE Part #6-1879354-1
RR03 5% 100R AMMO



TE Part #CAT-D9934-A78A
DYNAMIC 4000 REC AND TAB HSG



TE Part #770902-1
MINI UMNL SOCK 26-22 AWG SN



Documents

Product Drawings

PT78A2P

English

CAD Files

Customer View Model

ENG_CVM_CVM_2071566-4_1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2071566-4_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2071566-4_1.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ACCESSORIES FOR MINIATURE RELAY PT

English

Agency Approvals

CE Declaration of Conformity

English