



Connectors > Lighting Connectors > LED Holders



Lighting Connector Features Included: **Not Optic Compatible, Zhaga Inspired**

Operating Voltage: **60 VDC**

Termination Method to Wire & Cable: **Poke-In**

Connector System: **Wire-to-Component**

Number of Positions: **2**

Features

Housing Features

| | |
|------------------|--------|
| Housing Material | PBT GF |
|------------------|--------|

Operation/Application

| | |
|---------------------|-------|
| Circuit Application | Power |
|---------------------|-------|

Contact Features

| | |
|--------------------------------------|--------------|
| Contact Mating Area Plating Material | Gold |
| Contact Base Material | Copper Alloy |
| Contact Current Rating (Max) | 3 A |

Product Type Features

| | |
|-----------------------------------|-------------------|
| COB Substrate Thickness | 1 mm |
| LED Holders Product Type | LED Holder |
| Connector System | Wire-to-Component |
| Connector & Contact Terminates To | Wire & Cable |

Electrical Characteristics

| | |
|--|--|
| | |
|--|--|



| | |
|----------------------|--------|
| Current Rating (Max) | 3 A |
| Operating Voltage | 60 VDC |

Configuration Features

| | |
|--------------------------------------|--------------------------------------|
| Lighting Connector Features Included | Not Optic Compatible, Zhaga Inspired |
| Number of Positions | 2 |

Termination Features

| | |
|------------------------------------|---------|
| Termination Method to Wire & Cable | Poke-In |
|------------------------------------|---------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|-----------------------------|----------------------------|

Other

| | |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance | Compliant |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2213678-3
Z35 MINI LED HOLDER 12*15MM
PANHEAD

TE Part # 2213678-5
Z35 MINI LED HOLDER 13.5*13.5MM
PANHEAD

Also in the Series | LUMAWISE LED Holders

LED Holders(70)

Customers Also Bought

TE Part #5745171-5
AMPL CBL CLMP KIT SZ 1

TE Part #2213678-5
Z35 MINI LED HOLDER 13.5*13.5MM
PANHEAD

TE Part #1676480-3
CRG0402 1% 10K

TE Part #1SNK505910R0000
ES4

TE Part #1SNK900001R0000
BAM4

TE Part #3-2213678-4
Z35 MINI LED HOLDER 12*15MM
COUNTERSUNC

TE Part #1SNK505064R0000
ZS4-BR

TE Part #1SNK506022R0000
ZS6-4S-BL



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213678-4_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213678-4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213678-4_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

LUMAWISE LED Holder Type Z35

English

LUMAWISE LED Holder Type Z35

Product Specifications

Application Specification

English

Application Specification

English

Agency Approvals

KEMA Certificate label

English