

1838893-3

✓ ACTIVE


M12 Connector

TE Internal #: 1838893-3

5 Position Circular Connector, Wire-to-Panel, Sealable, Wire & Cable, Signal, Panel Mount, Reverse Gender, Plastic, Code A, Polyamide, M12 Connector

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 5

Connector System: **Wire-to-Panel**Sealable: **Yes**Connector & Contact Terminates To: **Wire & Cable**Contact Current Rating (Max): **5 A****Features****Electrical Characteristics**

Operating Voltage	500 VAC
-------------------	---------

Packaging Features

Packaging Quantity	50
--------------------	----

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Industry Standards

Compatible With Approved Standards Products	IEC
---	-----

Usage Conditions

IP Water Sealing Level	IP67
------------------------	------

Operating Temperature Range	-40 – 85 °C [-40 – 185 °F]
-----------------------------	----------------------------

Body Features

O-Ring Material	EPDM
-----------------	------

Environmental Protection	IP67
--------------------------	------

Environmental Protection Type	Sealed
Primary Product Color	Black
Shell Base Material	Plastic
Circular Connector Insulation Material Type	Polyamide
Hermetically Sealed	Yes

Mechanical Attachment

Panel Mount Feature	With
Mating Retention Type	Threaded
PCB Mount Retention	With
Panel Mount Feature Type	Screw Nut
Mating Alignment	With
PCB Mount Alignment	With
Connector Mounting Type	Panel Mount
Polarization Code	A
Mating Alignment Type	Keyed
Mating Retention	With

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal
Shielded	No

Product Type Features

Assembly Requirement	Factory Assembled
Circular Connector Shell Type	All Plastic
Connector Product Type	Connector Assembly
Assembly Type	Electrical Connector
Prewired	No
Connector System	Wire-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Plastic

Configuration Features

Keying & Polarized Position Locations	A
---------------------------------------	---

Factory Installed Backshell	With
Number of Positions	5
Number of Power Positions	0
Number of Signal Positions	5
Contacts Preloaded	Yes

Contact Features

Contact Current Rating (Max)	5 A
Reverse Gender	Yes
Circular Connector Contact Type	Pin

Housing Features

Circular Connector Shell Size	18
-------------------------------	----

Dimensions

Wire Size	24 – 20 AWG
-----------	-------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # T4133012041-000
M12, FRONT MOUNT, FEMALE, A, 4P,
SOLDER WIRE

Also in the Series | M12 Connector




Connector Hardware(11)



Connector Seals & Cavity Plugs(4)



M8/M12 Cable Assemblies(230)



Standard Circular Connectors(793)

Customers Also Bought



TE Part #T4110012051-000
M12 F, 5P GOLD A_CODE S
SHIELDED PG9





TE Part #175164-1
250 PL EX REC. 18-14AWG ST



TE Part #T1500163000-000
H16B-AG-LB



TE Part #T1330160140-000
H16B-TSH-RO-M40

TE Part #5677894004
RNF-3000-39/13-9-SPTE Part #T4151210005-003
RPC-M12-MR-5CON-PVC-1.5TE Part #1SNA176230R0200
BJM5D-10TE Part #CT02933001
CL105-7X2X0.75-PO-0CK5500TE Part #1SNA110368R1200
DR4/8.SFTE Part #1SNA164716R2100
BA2

Documents

Product Drawings

M12 Mtl MALE PNL CONN. Sldr Re

English

CAD Files

Customer View Model

[ENG_CVM_1838893-3_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1838893-3_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1838893-3_C.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_CVM_1838893-3_D.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1838893-3_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1838893-3_D.3d_igs.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

Product Specifications

Application Specification

English