



Connectors > Audio & Video Connectors > HDMI Connectors



Connector & Housing Type: **Receptacle**

Connector Profile: **Standard**

Number of Ports: **1**

PCB Mount Location: **Top**

PCB Mount Orientation: **Perpendicular Right Angle**

Features

Dimensions

PCB Thickness (Min)	1.6 mm[.063 in]
---------------------	-----------------

Packaging Features

Packaging Method	Tray
------------------	------

Contact Features

Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.38 µm[15 µin]
Contact Current Rating (Max)	.5 A

Housing Features

Housing Color	Black
Centerline (Pitch)	1 mm[.039 in]

Usage Conditions

Mating Cycles (Max)	10000
Soldering Temperature (Max)	240 °C
Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]



Termination Features

Termination Post & Tail Length	2.3 mm[.091 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention Type	Kinked Legs, Straight Leg
PCB Mount Alignment Type	Locating Posts
PCB Mount Location	Top
Connector Mounting Type	Board Mount

Configuration Features

Stacked	No
Number of Ports	1
PCB Mount Orientation	Perpendicular Right Angle
Number of Positions	19

Body Features

Shell Plating Material	Tin
Shell Plating Finish	Matte
Connector Profile	Standard

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1770019-6
CABLE ASSY, HDMI

Customers Also Bought


TE Part #5145167-4
STANDARD EDGE .050 SERIES 60
DUAL ASSY

TE Part #6469001-1
HM-ZD 4PR RECP 80P


TE Part #3-1827231-6
.5FHR04H,440,B,GIG,08/Sn,HT,NS

TE Part #294762-E
STVC/2 48 F ABC VVV 7-00 EE 2,9 *
247 E0







TE Part #4-160970-1
CABLE TY 200X2.6 NAT




TE Part #484290-E
MSPEED 50 M SMD M10 BE AB VV
137 094 * 2




TE Part #2-2176467-1
TLRP 1206 1.0W R040 1% 75PPM 5K RL



TE Part #3544444-E
STVE 48 F ACE GGG 7-01 EE 6,0 * 207
E 17



TE Part #494153-E
STVR/2 48 MI ABC VVV 4-00 GA06 2,5
* 247



TE Part #7-1768414-5
LBG-U-03235/EET613620/SET-T1K

Documents

Product Drawings

Std HDMI, Flag, T/H

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2007435-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2007435-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2007435-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

6-1773453-4_HDMI_QRG

English

Product Specifications

Application Specification

English