



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Connectors



FFC Connector Product Type: **Connector Assembly**

Connector System: **Wire-to-Board**

Number of Positions: **14**

Centerline (Pitch): **2.54 mm [.1 in]**

Number of Rows: **1**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Electrical Characteristics

Operating Voltage	150 VAC
Insulation Resistance	500 MΩ

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.94 mm[.155 in]

Dimensions

PCB Thickness (Recommended)	2.36 mm[.093 in]
-----------------------------	------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Mechanical Attachment

Mating Retention Type	Latch
PCB Mount Retention	Without
Mating Retention	With
Mating Alignment	Without
Panel Mount Feature	Without
Connector Mounting Type	Board Mount



Packaging Features

Packaging Quantity	12
Packaging Method	Tube

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Thickness	3.81 µm
Contact Type	Socket
Contact Current Rating (Max)	1 A

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]
FFC Cable Entry	Vertical

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector & Housing Type	Receptacle
FFC Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Insertion Force Type	Zero Insertion Force (ZIF)

Configuration Features

Number of Positions	14
Number of Rows	1
PCB Mount Orientation	Vertical

Body Features

Primary Product Color	Black
-----------------------	-------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | ZIF LINE



Customers Also Bought



TE Part #5-1775444-2
EMIX CONN., 1.5MM PITCH, HDR, R /A, 2P



TE Part #8-320553-1
PIDG R 22-16 COMM 22-18 MIL 4



TE Part #2-328527-1
TERMINAL,PG R 16-14 8




TE Part #41290
250 FASTON,TAB,BR




TE Part #4-2176339-6
CRGCQ 0603 56K 1%




TE Part #NT-SMA-N
Nut Nickel SMA Connectors RoHS



TE Part #1-480416-8
250 FASTON HSG.,REC.,1 POS, NATRUAL



TE Part #42025-1
250 FASTON REC 18-14 AWG TPBZ



TE Part #58524-2
PROCrimper DIE



TE Part #5053242179
RNF-100-3/4-BK-STK

Documents

Product Drawings

14 ZIF LINE ASSY .100C/L

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_487925-2_G4.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_487925-2_G4.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_487925-2_G4.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

ZIF 50 Flat Flexible Discrete Wire Connectors

English

Application Specification

English