



EMI & EMC Solutions > EMI Filters > Power Entry Modules > CORCOM P SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry Module**

Input Voltage Selection: **Single AC**

Filter Switch Type: **DPST**

Filter Shield Type: **None**

Product Orientation: **Vertical**

[All CORCOM P Series Multi-Function Inlet Fil \(261\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Dimensions

Panel Thickness (Recommended)	.13 – 1 mm
-------------------------------	------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Configuration Features

Extender Options	None
Fuse Options	Single

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	DPST



Output Termination Type	.187" FASTON
Filtering Requirements	Unfiltered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Input Voltage Selection	Single AC
Leakage Current (Max) (120VAC, 60Hz)	2 µA
Leakage Current (Max) (250VAC, 50Hz)	5 µA
Current Rating	10 A
Operating Voltage	250 VAC

Body Features

Filter Shield Type	None
Product Orientation	Vertical

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits




as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1609140-3
PA105 J0=F6806



TE Part # 1609146-2
PA102 CONNECTOR PIN=F6999




TE Part # 1609146-1
PA101 CONNECTOR PLU=F6998




TE Part # 1609140-1
PA100=F6800

Also in the Series | Corcom P



EMI & EMC Accessories(4)



Power Entry Modules(317)

Customers Also Bought



TE Part #2-1703498-3
2POS, MCON 1.2 LL TAB SEALED
COD B



TE Part #1996705-4
8 Pos RF Mod, DaughterCard, SMPM,
VITA67.2



TE Part #1996771-1
SMPM STR CBL JACK



TE Part #2102771-1
DC, 7Row, Center, MULTIGIG RT 2R



TE Part #1-66359-5
III+ PIN, 18-14, TIN, STRIP




TE Part #2213772-3
AV22 SPM 3A MOVE RING LED
WHITE 24V



TE Part #1-66358-8
III+ SKT, 18-14, TIN, STRIP



TE Part #1630020-6
NHSC200 1R5 5%



Documents

Product Drawings

[PE0S0SBX0=C1164](#)

English

CAD Files

Customer View Model

[ENG_CVM_6609102-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_6609102-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_6609102-1_A.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_6609102-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6609102-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6609102-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

PE0S0SBX0

Power Entry Module, Single AC Input, DPST, None, Vertical, 10 A, .187" FASTON
Output, 250 VAC, Unfiltered, IEC 320/C-14, Corcom P, Power Entry Modules

