




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1 – 2.5 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	8.1 kgf

Other

Line	Premier
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Dimensions

Product Length	19 mm[.748 in]
Compatible Insulation Diameter Range	3 – 4.3 mm[.118 – .169 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	1 – 2.5 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Steel
Terminal Plating Material	Pre-Nickel
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 63892-1
250 FASTON REC 16-12 AWG NPST

TE Part # 2150234-1
OCEAN_2.0_APPLICATOR-E-110F180F-REM

TE Part # 2150234-2
OCEAN_2.0_APPLICATOR-E-110F180F-REA

TE Part # 7-2150234-7
OCEAN_2.0_SPARE_PART_KIT-110F180F

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(134)

Quick Disconnects(425)

Splices(4)



Customers Also Bought

TE Part #4-6609089-0
16WGB1=F4338A

TE Part #640582-1
08P UMNL PLUG HSG

TE Part #926883-1
UNIVERSAL M-N-L PIN

TE Part #926882-1
UMNL SOK 20-14 PTPBR

TE Part #63301-1
250 FASTON TAB 22-15 AWG NPST

TE Part #63300-1
312 FASTON TAB 22-15 AWG NPST

TE Part #63677-1
312 FASTON REC 16-12 AWG TPBR

TE Part #ASL006-05PB-HE
RECEPT.ASSY. 2 HOLE MNT.MICRO MK3

TE Part #LBT3400LS
MOUNT,TKG,3/4

TE Part #926539-1
250 FASTON HSG. REC. 1P NATURAL

Documents

Product Drawings

250 FASTON,REC.,17-14 AWG,PNST

English

CAD Files

Customer View Model

ENG_CVM_CVM_4-160256-2_CS.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-160256-2_CS.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-160256-2_CS.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English

Application Specification

English

Agency Approvals

UL Report

English