



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 3.31 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Other

Line	Premier
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features



Packaging Quantity	4000
Packaging Method	Strip/Reel

Dimensions

Product Length	17.02 mm[.67 in]
Compatible Insulation Diameter Range	2.79 – 5.33 mm[.11 – .21 in]
Terminal Material Thickness	.43 mm[.017 in]
Wire Size	.82 – 3.31 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	Tab-Lok
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2232111-3 250 FASTON,FLAG,REC.,12-20 AWG, TPBR	 TE Part # 2232111-1 250 FASTON,FLAG,REC.,12-20 AWG, TPBR	 TE Part # 1852633-1 EAPOH160TABLOCK180O LM/G-HINGE BAR	 TE Part # 1596696-2 HB APPL,AOL
 TE Part # 565504-3 STD HBEMPR160T220OK	 TE Part # 1855041-1 HINDGE BAR F.A. EMPO160TAB180O LM & G	 TE Part # 565504-1 STD HBEMPR160T180OK	 TE Part # 1596697-5 HB APPL,AOM
 TE Part # 2088156-2 MINI APPLICATOR, HINGE BAR END FEED	 TE Part # 7-1855041-7 SPARE PART KIT		

Also in the Series | FASTON 250

 Compression Connectors(4)	 Crimp Terminal Housings(132)	 Insertion & Extraction Tools(6)	 Magnet Wire Terminals(1)
 PCB Terminals(134)	 Quick Disconnects(425)	 Splices(4)	

Customers Also Bought

 TE Part #1-320627-0 N PIDG RING 16-14 HD 8	 TE Part #61375-1 250 FASTON REC 18-14 AWG TPBR	 TE Part #61944-2 250 FASTON REC 18-14 AWG TPBR	 TE Part #42801-2 187 FASTON REC 20-16 AWG TPBR
 TE Part #41333 RING 18-14 AWG TPBR	 TE Part #41450 250 FASTON REC 14-10 AWG TPBR	 TE Part #2-1393117-9 KUP-11A55-120=KU	 TE Part #7-1393118-0 KUP-5D55-12=KU
 TE Part #520197P044 RT-3-NO.2-0-1.125IN	 TE Part #2213847-1 GASKET, SEALING ROT DIM RECEPT		

Documents

Product Drawings

250 FASTON FLAG REC 18-12 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_41532_DS.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_41532_DS.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_41532_DS.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Engineering Report

English

Agency Approvals

Agency Approval Document

English