



Connectors > Power Connectors > Panel & PCB Outlets



Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **15 A**

Housing Color: **Gray**

Wire Size: **12 AWG, 14 AWG**

Housing Material: **Nylon**

Features

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Configuration Features

Number of Positions	3
---------------------	---

Termination Features

Termination Method to Wire & Cable	FASTON Tab
------------------------------------	------------

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Body Features

Cover Color	Black
Cover Material	Nylon

Operation/Application

Circuit Application	Power
---------------------	-------

Housing Features

Centerline (Pitch)	12.7 mm[.5 in]
Housing Color	Gray
Housing Material	Nylon

Contact Features

Contact Base Material	Brass
-----------------------	-------



Contact Current Rating (Max)	15 A
------------------------------	------

Product Type Features

Connector System	Cable-to-Panel
Connector & Contact Terminates To	Wire & Cable

Dimensions

Wire Size	12 AWG, 14 AWG
Product Height	26.9 mm[1.06 in]
Product Width	26.9 mm[1.06 in]
Product Depth	30.3 mm[1.19 in]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 796285-1
HOUSING,CONV OUTLET,DUMMY

TE Part # 62531-1
205 FASTON TAB 18-14 AWG TPBR

Customers Also Bought

TE Part #1462051-2
HF353=50OHM140MW 5V MONO

TE Part #1326978-1
BACK SHELL, 2 WIRE, AMPSEAL 16

TE Part #208979-2
CONV OUTLET ASSY (BLACK)

TE Part #62419-3
SPLICE 18-16/18-14 AWG .020 NPST

TE Part #5550024014
NT-3/8-0-SP

TE Part #1-1719102-1
PCB 6.3 TERMINAL

TE Part #771113P006
FL2500-NO.2-I9-0-65MM

TE Part #1633615-1
ANVIL, COMB W/ JOG, SPEC AMP-IN SLOT

TE Part #1SNA233131R1400
RC610 L1-L2-L3-N-PE (X20)
HORIZONTAL

TE Part #216906-1
.250 POWER TERM.A.P

Documents

Product Drawings
CONV OUTLET ASSEMBLY (GRAY)

English

CAD Files
Customer View Model



[ENG_CVM_CVM_1-208979-1_AE.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-208979-1_AE.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-208979-1_AE.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC08_AC_INPUTS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English