



Terminals & Splices > Splices



Splice Type: **Butt Splice**

Wire Size: **.12 – .4 mm²**

Sealable: **No**

Splice Features: **Serrated**

Features

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Contact Features

	100 µin
Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed

Body Features

Product Weight	.142 g
Splice Features	Serrated

Dimensions

Outside Diameter	1.96 mm[.077 in]
Wire Size	202 – 810 CMA
Barrel Inside Diameter	.86 mm[.034 in]



Terminal Material Thickness	.51 mm[.02 in]
Product Length	9.78 mm[.385 in]

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



REPRESENTATION ONLY

TE Part # 69363
DAHT STRATO SOLIS 26-20 ASSY


Customers Also Bought



TE Part #8-328998-1
TERMINAL,PIDG R 16-14 5/16



TE Part #87631-1
06 MODIV HSG COMP DR .100 POL



TE Part #33695
TERMINAL,BUDG R 26-22 2



TE Part #4-1625867-7
RP 1J 0.166W 18R7 0.1% 25PPM 1K RL



TE Part #4-1625867-9
RP 1J 0.166W 19R6 0.1% 25PPM 1K RL




TE Part #6-2176364-5
RQ 0402 21K5 0.1% 10PPM 5K RL



TE Part #CAT-R21-567014
Low Profile HS Boots: Blow Molded, Slim Line, Lipped, Straight



TE Part #NB-PTCO-172
Pt100, 2.0x4.0, Class B, PTFE101B1G0



Documents

Product Drawings

SPLICE, BUTT, BUDGET, 26-22

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_321024_U.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_321024_U.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_321024_U.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English