

SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, straight, SPEEDCON, M23, number of positions: 5+PE, contact connection type: Pin, Axial O-ring, 4x Ø 3.2, shielded: yes, flange dimensions: 26 mm x 26 mm, number of positions: 6, connection method: Crimp connection, series: SF

Commercial data

Item number	1617909
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB32
Product key	ABRBFL
GTIN	4046356581035
Weight per piece (including packing)	37.915 g
Weight per piece (excluding packing)	35.63 g
Customs tariff number	85366990
Country of origin	DE

SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

Technical data

Notes

Order information:	Order crimp contacts 6 x Ø 2 mm separately
Safety note	
Safety note	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.• The products are suitable for applications in plant, controller, and electrical device engineering.• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Operate the connector only when it is fully plugged in and interlocked.• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.• Observe the minimum bending radius of the cable. Lay the cable without twisting it.• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting

SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

Mounting

Mounting type	Front mounting
Mounting	4x Ø 3.2

Product properties

Product type	Circular connectors (device side)
Series	SF
Application	Power
Number of positions	6
Connection profile	5+PE
Shielded	yes
Coding	N
Thread type	M23

Dimensions

Housing	
Flange dimensions	26 mm x 26 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	FPM
Housing material	GD-Zn

Electrical properties

Contact	
Contact diameter	2 mm
Max. current	30 A
Nominal voltage U _N	630 V
Overshoot category	III
Degree of pollution	3
Rated surge voltage	6 kV

Contact	
Contact diameter	2 mm
Max. current	9 A
Nominal voltage U _N	250 V
Overshoot category	III
Degree of pollution	3
Rated surge voltage	4 kV

Connection data

Conductor connection	
----------------------	--

SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

Connection method	Crimp connection
Contact connection type	Pin

Connector

Type	straight
------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Altitude	3000 m
Permissible humidity (storage/transport)	50 % ... 65 %

SF-5EP1N8AWA00S - Device connector front mounting




1617909

<https://www.phoenixcontact.com/us/products/1617909>

Drawings

Schematic diagram



Connector pin assignment


SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

Dimensional drawing



Installation dimensions


SF-5EP1N8AWA00S - Device connector front mounting



1617909


<https://www.phoenixcontact.com/us/products/1617909>

Dimensional drawing



Dimensional drawing

Diagram



SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1617909>

 cUL Recognized Approval ID: E153698-20041116	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	18 A	12 - 12	-

 UL Recognized Approval ID: E153698-20041116	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	27 A	12 - 12	-

cULus Recognized

SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SF-5EP1N8AWA00S - Device connector front mounting



1617909

<https://www.phoenixcontact.com/us/products/1617909>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com