




Positive Lock | Positive Lock 250

TE Internal #: 170265-2

Quick Disconnect Receptacle, 20 – 14 AWG, .51 – 2.08 mm² Wire, 6.35 mm [.25 in] Tab Width, Straight, Brass, Tin Plating, Positive Lock 250

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	.7 – 10.2 kgf

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Dimensions



Product Length	23 mm[.905 in]
Compatible Insulation Diameter Range	2.2 – 3.4 mm[.086 – .134 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.51 – 2.08 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 752940-1
CRIMPING JAW HEAD ASSY



TE Part # 171809-1
POSITIVE LOCK (PL) HOUSING



TE Part # 927853-8
PL 250 REC 20-17 AWG AgBR



TE Part # 928901-3
PL 250 REC TERMINAL 17-13 AWG
TPBR LP




TE Part # 171809-2
POSITIVE LOCK (PL) HOUSING



TE Part # 928901-4
PL 250 REC TERMINAL 17-13 TPPB LP



TE Part # 784640-1
EXT TOOL FOR POS LOCK MKI



TE Part # 1337265-1
POS LOCK RECEPTACLE GOLD



TE Part # 755342-1
DAHT POS LOCK REC CONT 20-14
ASSY

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(184)



Insertion & Extraction Tools(3)




Insulation Boots & Sleeves(4)




Quick Disconnects(185)


Customers Also Bought



TE Part #281839-5
HOUSING HE13 HE14 COSI 2X5 P



TE Part #61165-1
BUTTON CONTACT 20-16 AWG BR



TE Part #1658526-5
609-1041LF FEM SOCKET, LEAD FREE



TE Part #1SNK706012R0000
ZK4-4P




TE Part #1SNK708011R0000
ZK6-3P



TE Part #2176371-3
RQ 0603 4K87 0.1% 10PPM 5K RL



TE Part #9-1879507-9
CRGH0603 1% 120R 0.2W



TE Part #7-1879265-3
RP 2B 249K 0.1% 15PPM CUT LENGTH



TE Part #1-1609034-5
10VSB1=F8331



TE Part #1SNK708911R0000
EK6-3P

Documents



Product Drawings

PL 250 REC 12-10 AWG 0.406 X 42.3

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170265-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170265-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170265-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

1-Position, Positive Lock Connector

English