



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **2**
Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Dimensions

Connector Width	7.62 mm[.3 in]
PCB Thickness (Recommended)	3.18 mm[.125 in]
Connector Height	13.97 mm[.55 in]
Connector Length	13.97 mm[.55 in]
Profile Height from PCB	14.73 mm[.58 in]

Packaging Features

Packaging Quantity	200
Packaging Method	Bag

Industry Standards

Compatible With Agency/Standards Products	UL, VDE, CSA
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476



Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Diameter	1.57 mm[.062 in]
Termination Post & Tail Length	5.09 mm[.2 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 1.79 µm[50 – 70 µin]
Contact Size	2.95mm
Contact Mating Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
PCB Contact Termination Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
Contact Shape & Form	Round
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material	Pre-Tin
Contact Type	Socket
Contact Current Rating (Max)	12 A

Housing Features

--



Mating Entry Location	Top
Housing Material	Nylon
Centerline (Pitch)	6.35 mm [.25 in]

Configuration Features

Number of Columns	2
Number of Loaded Positions	2
Number of Power Positions	2
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	White
-----------------------	-------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability


Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 2178649-1 2P UMNL CAP HSG, GW	 TE Part # 350811-1 STR/REL CLAMP	 TE Part # 1703062-3 CAP, 2 CIRCUIT , UNIVERSAL MATE-N-LOK	 TE Part # 350777-1 02P UMNL PLUG HSG
 TE Part # 2178649-3 2P UMNL CAP HSG, GW	 TE Part # 1703062-2 CAP, 2 CIRCUIT , UNIVERSAL MATE-N-LOK	 TE Part # 794269-1 02P UMNL INTERFACE SEAL	 TE Part # 1586856-1 02P UMNL CAP HSG, GW



TE Part # 794270-1
02P UMNL WIRE SEAL



TE Part # 1-640719-1
02P UMNL STR/REL NATL



TE Part # 640713-1
02P UMNL STR/REL & INSERT




TE Part # 2-480699-0
02P UMNL CAP HSG NATL




TE Part # 794991-1
02P UMNL BLACK INTERFACE SEAL




TE Part # 1703062-1
CAP, 2 CIRCUIT , UNIVERSAL MATE-N-LOK



TE Part # 350848-2
02P UMNL PLUG TEST ASSY 94VO




TE Part # 1-640719-0
02P UMNL STR/REL & INSRT NATL




TE Part # 770017-1
02P UMNLII IN-LNE PLUG HSG KIT



TE Part # 1-350589-0
STR/REL CLAMP NATL



TE Part # 640713-2
02P UMNL STR/RELIEVE



TE Part # 2178649-2
2P UMNL CAP HSG, GW

Also in the Series | **Universal MATE-N-LOK**



Connector Caps & Covers(34)



Connector Contacts(209)




Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)



Insertion & Extraction Tools(4)



PCB Headers & Receptacles(284)



Power Contacts(209)



Wire-to-Board Headers & Receptacles (284)

Customers Also Bought



TE Part #2-6609128-8
[6VM1S=F8096](#)




TE Part #1609078-1
[6ESRM-P=F6990](#)



TE Part #5745783-5
[25 MSFL RCPT RA 318 \(SL,FM\)](#)



TE Part #350829-1
[12P UMNL HDR ASSY PC 94VO](#)



TE Part #6-215882-4
[64 WAY GREY MK II RECP](#)



TE Part #CAT-MIPS0044
[MV Pressure Sensor, Uncalibrated, 87NU](#)



TE Part #TRA4503
[OMNI,PH,NMO,450-470 WHT,3,150,3 /4 MT](#)



TE Part #G8BI
[MOUNT,MGM,3/4,58A,BNCM I,CMP, CHR,STD,12F](#)



TE Part #LAIL350NN
[SURGE,NN,0-1000MHZ INLINE](#)

Documents

Product Drawings

[02P UMNL HDR ASSY PC 94VO](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_350831-1_T.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_350831-1_T.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_350831-1_T.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_350831-1_N1.3d_igs.zip](#)

English



Customer View Model

[ENG_CVM_350831-1_N1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_350831-1_N1.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL](#)

English