




Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**
Element Type: **Wire Wound, Ceramic Composition**
Power Rating: **3 W**
Resistance Class: **1kΩ – 1MΩ**
Resistance Value: **2.2K Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±300 ppm/°C

Electrical Characteristics

Operating Voltage	500 V
Power Rating	3 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	2.2K Ω
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound, Ceramic Composition

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2



Dimensions

Passive Component Dimensions	17.5 x 6.5 mm
------------------------------	---------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2176079-5
EP 3W 47R 5%

TE Part # 8-2176612-1
EP 3W (SS) 2K2 5%

TE Part # 2176085-7
EP 9W (S) 100R 5%

TE Part # 2176083-1
EP 5W (S) 10R 5%

TE Part # 2176084-7
EP 7W (S) 100R 5%

TE Part # 2176081-7
EP 1W (S) 100R 5%

Also in the Series | **Neohm EP**

[Through-Hole Resistors\(607\)](#)

Customers Also Bought

TE Part #1-1393210-2
T9AS1D12-110

TE Part #3-2176057-0
RLP73K 3A R16 1% 1K RL

TE Part #1-284513-0
10 POS TERMI-BLOK HDR 900 POL.


TE Part #1393128-5
PRD-5AY0-120=PRD

TE Part #102312-1
UNIVERSAL HEADER LATCH


TE Part #3-794638-8
08P MICRO MNL ASSY,VRT,SMT,LF

TE Part #1-1546671-0
10P.437" DR BARRIER,W/WIR CLMP

TE Part #9-1393104-8
KRPA-5AG-120=KRPA



TE Part #2118059-1
WIMAX SINGLE BAND PCB Antenna



TE Part #3-1768036-0
PRP35-20BL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2176079-5_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176079-5_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176079-5_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Wirewound Anti Surge Resistors - Type EP Series

English