

2198325-2  ACTIVE


TE Internal #: 2198325-2

zSFP+ Stacked (SFP28), Cage Assembly with Integrated Connector,
.8mm [.032in] Centerline, Signal

[View on TE.com >](#)



Connectors > Pluggable I/O Connectors & Cages > zSFP+ Stacked Cage Assembly: Gasket



Form Factor: **zSFP+ Stacked (SFP28)**

Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**

Centerline (Pitch): **.8 mm [.032 in]**

Sealable: **No**

Circuit Application: **Signal**

[All zSFP+ Stacked Cage Assembly: Gasket \(34\)](#)

Features

Industry Standards

UL Flammability Rating

UL 94V-0

Termination Features

Termination Method to PCB

Through Hole - Press-Fit

Termination Post & Tail Length

1.8 mm[.07 in]

Dimensions

PCB Thickness (Recommended)

1.5 mm[.059 in]

Contact Features

Contact Mating Area Plating Material

Gold or Gold Flash over Palladium Nickel

Tail Plating Material

Tin

Contact Mating Area Plating Material Thickness

.76 μ m[29.92 μ in]

Packaging Features

Packaging Method

Tray

Configuration Features

Lightpipe Style	Standard
Number of Positions	80
Number of Ports	4
Port Matrix Configuration	2 x 2

Operation/Application

Pluggable I/O Applications	SFP+ Thermally Enhanced
Heat Sink Compatible	No
Circuit Application	Signal

Housing Features

Cage Material	Nickel Silver Alloy
Centerline (Pitch)	.8 mm[.032 in]

Product Type Features

Cage Type	Stacked
Form Factor	zSFP+ Stacked (SFP28)
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Sealable	No

Electrical Characteristics

Data Rate (Max)	32 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Elastomeric Gasket
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JUNE 2024

(241)

Candidate List Declared Against: JUNE
2024 (241)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900
ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 4-2821224-5
SFP56 DIRECT ATTACH CA, 3M,
26AWG



TE Part # 2334985-2
SFP28 DIRECT ATTACH CA, 1M,
32AWG



TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly:
30 AWG



TE Part # CAT-C11-N49011
SFP28 to SFP28 Cable Assembly:
26 AWG




TE Part # CAT-C11-N49033
QSFP28-Four SFP+ Cable Assembly:
30 AWG



TE Part # CAT-Q17-N49033
QSFP56-Four SFP56 Cable Assembly:
26 AWG




TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly:
26 AWG



TE Part # 4-2334985-2
SFP56 DIRECT ATTACH CA, 1M,
32AWG



Customers Also Bought



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2198325-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2198325-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2198325-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[zSFP+ Interconnect Brochure](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English