

2350202-1

✓ ACTIVE

SFP28

TE Internal #: 2350202-1


zSFP+, Cage Assembly, Signal, Operating Temperature Range -55

- 105 °C [-67 – 221 °F], Data Rate (Max) 32 Gb/s, 3 Ports

[View on TE.com >](#)



Connectors > Pluggable I/O Connectors & Cages > zSFP+ Cage Assembly: EMI Springs



Form Factor: **zSFP+**

Pluggable I/O Product Type: **Cage Assembly**

Sealable: **No**

Circuit Application: **Signal**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

[All zSFP+ Cage Assembly: EMI Springs \(24\)](#)

Features

Industry Standards

UL Flammability Rating

UL 94V-0

Termination Features

Termination Method to PCB

Through Hole - Press-Fit

Termination Post & Tail Length

2.05 mm

Dimensions

PCB Thickness (Recommended)

2.25 mm

Contact Features

Contact Current Rating (Max)

.5 A

Contact Underplating Material

Nickel

Contact Mating Area Plating Material

Gold

PCB Contact Termination Area Plating Material

Gold Flash

Housing Features

Cage Material

Stainless Steel

Packaging Features

Packaging Method	Tray
------------------	------

Product Type Features

Cage Type	Ganged
Form Factor	zSFP+
Pluggable I/O Product Type	Cage Assembly
Sealable	No

Configuration Features

Number of Ports	3
Port Matrix Configuration	1 x 3

Electrical Characteristics

Data Rate (Max)	32 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per

Solder Process Capability	homogenous material. Also BFR/CFR/PVC Free
---------------------------	--

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1761394-1
DUST COVER, SFP, GANGED &
STACKED

Customers Also Bought



TE Part #1658690-1
HDP-22,RCPT,SIZE 1,15 POSN,CLI



TE Part #2110304-1
SFP+ 1x1 Cage Assembly, Solder Tail



TE Part #280377-2
2P MODU II SHRD HDR,RT ANG, 0.38
AU



TE Part #280378-2
4P MODU II SHRD HDR, RT ANG, 0.38
AU



TE Part #1-1393225-7
RY611005



TE Part #1-292303-6
Std USB Type A, R/A, SMT, Offset



TE Part #2173239-1
1x3 Cage Assy Bhnd Bzl QSFP28



TE Part #2301994-7
RJ45 JACK INT.MAG. 1GB 1X1



TE Part #1658691-1
HDP-22, PLUG, SIZE 1, 15 POSN, CLI



TE Part #2227303-3
CAGE ASSEMBLY, SFP, .071 TAIL

Documents

Product Drawings

ZSFP+ 1X3 CAGE ASSEMBLY, EON

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2350202-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2350202-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2350202-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English