




Connectors > PCB Connectors > Card Edge Connectors > PCI & PCI Express Connectors



Connector System: **Board-to-Board**

Number of Positions: **184**

Centerline (Pitch): **1.27 mm [.05 in]**

Termination Post & Tail Length: **3.18 mm [.125 in]**

Contact Mating Area Plating Material Thickness: **[30 µin]**

Features

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Electrical Characteristics

Operating Voltage	203 VAC
-------------------	---------

Industry Standards

Bus Type	PCI
----------	-----

Packaging Features

Packaging Method	Box
Packaging Quantity	35

Dimensions

PCB Thickness (Accepted)	1.57 mm[.062 in]
Connector Length	128 mm[5.039 in]
Connector Height	15.5 mm[.613 in]
Connector Width	8.88 mm[.35 in]

Body Features

Product Weight	26.406 g
Primary Product Color	Natural

Contact Features

Contact Current Rating (Max)	1.1 A
PCB Contact Termination Area Plating Material Thickness	2.537 µm



Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
	30 µin

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.18 mm[.125 in]

Housing Features

Housing Material	High Temperature Thermoplastic
Centerline (Pitch)	1.27 mm[.05 in]

Configuration Features

Number of PCB Mount Retention Features	3
Number of Positions	184
PCB Mount Orientation	Vertical
Ejector	Without

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1734774-1
PCI EXP 3.1L 36 POS WHT G/F



TE Part # 1761842-1
CONNECTOR ASSY, 60 DUAL POSITI



TE Part # 5-2337939-4
PCIE GEN4 CON,SMT,164POS,30u", MYLAR,HT

Customers Also Bought



TE Part #1658543-2
SOCKET CONT DUPL PLT STRIP HD-



TE Part #2-324165-1
TERMINAL,PG SPD FLG 16-14 6



TE Part #640254-1
KEYING PLUG .045 SQ PST CONN




TE Part #1-2058703-2
Herm Blade& Recp Assy, 4 Pos,Latch





TE Part #4-2176217-9
CPF A 0805 10K 0.1% 25PPM 1K RL




TE Part #829082-000
462A423-51-0



TE Part #YDTS26W25-04PNV001
PLUG ASSY



TE Part #5536507-2
2MM FB,ASY,048,SIG,REC,SL,2.73



TE Part #87046-1
MOD IV RECP LP



TE Part #5536501-1
2MM FB,ASY,24,SIG,HDR,SL,4.25

Documents

Product Drawings

CONNECTOR ASSEMBLY, DUAL POSIT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5145166-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5145166-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5145166-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English