




Connectors > Lighting Connectors > Street Lighting Controls > Street Lighting Receptacles



Lighting Product Type: **Gasket**
EU RoHS Compliance: **Compliant**
EU ELV Compliance: **Compliant**

Features

Body Features

Primary Product Color	Black
-----------------------	-------

Product Type Features

Lighting Product Type	Gasket
-----------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-ST833-L97
Receptacle Assembly



TE Part # CAT-Z23-DRE
LUMAWISE Endurance N Poke-In:
Streetlight Dimming Receptacles


Also in the Series | LUMAWISE Endurance N



Street Lighting Accessories(18)




Street Lighting Base Assemblies(31)



Street Lighting Open & Shorting Caps
(3)



Street Lighting Power Management(6)




Street Lighting Receptacles(25)



Customers Also Bought



TE Part #3-643813-2
02P MTA100 CONN ASSY POL RIB



TE Part #643075-2
02P MTA100 MOLDED COVER



TE Part #2213130-2
LUMAWISE LED HOLDER Z50 STD
PROFILE 2024



TE Part #1-1625890-2
2W SM M/OX 5% 150R



TE Part #2328823-2
LUMAWISE S 80MM DIA DOME
SMOKE GRAY MED



TE Part #1-215460-2
MICRO-MATCH FEM.SE



TE Part #2834385-2
RELEASE POKE-IN
CONNECTOR_2P_NATURAL



TE Part #512986-000
EKM-2020-2D1-B



TE Part #2213831-3
BASE ASSY, 80MM, SEALED



TE Part #2388426-1
ASSEMBLY, SENSOR LUMAWISE
MOTION

Documents

Product Drawings
GASKET, PHOTOCCELL RECEPTACLE
English

Datasheets & Catalog Pages
LUMAWISE STREET LIGHT DIMMING AND CONTROL QUICK REFERENCE GUIDE
English
LUMAWISE DIMMING RECEPTACLE universal MATE-N-LOK Connectors
LUMAWISE DIMMING RECEPTACLE universal MATE-N-LOK Connectors
English
LUMAWISE DIMMING RECEPTACLE IEC 61984 - Double Insulation
LUMAWISE DIMMING RECEPTACLE IEC 61984 - Double Insulation
English
LUMAWISE Endurance N ANSI C136.41 Standard Dimming Receptacle Assembly
English
LUMAWISE Endurance N ANSI C136.41 Standard Dimming Receptacle Assembly



German

LUMAWISE Endurance N ANSI C136.41 Standard Dimming Receptacle Assembly

LUMAWISE Endurance N ANSI C136.41 Standard Dimming Receptacle Assembly

LUMAWISE Endurance N ANSI C136.41 Standard Dimming Receptacle Assembly

Product Specifications

Application Specification

English