



Connectors > Lighting Connectors > Street Lighting Controls > Street Lighting Connectors



Lighting Product Type: **Shorting Cap**
Primary Product Color: **Black**
Product Height: **29.6 mm**
Lighting Connector Features Included: **Keyed, Not Vented**
Compatible With Agency/Standards Products: **UL**

Features

Dimensions

Product Diameter	36.5 mm
Product Height	29.6 mm

Product Type Features

Lighting Product Type	Shorting Cap
Sealable	Yes

Body Features

Primary Product Color	Black
-----------------------	-------

Configuration Features

Lighting Connector Features Included	Keyed, Not Vented
Number of Positions	4

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Contact Features

--	--



Contact Current Rating (Max)	5 A
------------------------------	-----

Usage Conditions

Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2382635-1
LUMAWISE POWER INPUT TERMINAL BLOCK (TB)

TE Part # 1-2445583-1
LUMAWISE MOTION - LOGIC OUTPUT, CIRC.

TE Part # 2-2343404-1
MODULE, 80MM LUMAWISE ENDURANCE S,KEYED

TE Part # 2341474-2
SEALING CAP, RCPT, LUMAWISE ENDURANCE S

TE Part # 2341474-1
SEALING CAP, RCPT, LUMAWISE ENDURANCE S

TE Part # 1-2343404-1
MODULE ASSY,80MM LUMAWISE S, KEYED,vented

TE Part # 2445583-1
LUMAWISE MOTION - LOGIC OUTPUT, RECT.

TE Part # 2343405-1
MODULE,40MM LUMAWISE ENDURANCE S. KEYED

Also in the Series | LUMAWISE Endurance S

Poke-In Connectors(1)

Street Lighting Connectors(47)

Street Lighting Power Management(5)

Customers Also Bought

TE Part #2213626-1
GASKET, SEALING ROT DIM RECEPT

TE Part #5-1393243-9
RT424005

TE Part #1-1586041-2
12P VAL-U-LOK R/A HDR V2

TE Part #2213858-1
RECEPTACLE ASSEM., LUMAWISE ENDURANCE S

TE Part #1-2328823-2
LUMAWISE S 80MM DIA DOME CLEAR MEDIUM

TE Part #2213831-1
LUMAWISE ENDURANCE S BASE ASSEMBLY, 80MM

TE Part #1SNG601010R0000
EP-SG-M12-LGR-D

TE Part #12336-22
CONT IMP



Documents

Product Drawings

RECEPTACLE, LUMAWISE ENDURANCE S, KEYED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2343403-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2343403-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2343403-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

LUMAWISE STREET LIGHT DIMMING AND CONTROL QUICK REFERENCE GUIDE

English

Datasheet - Lumawise Z10

English

Lumawise Endurance S Modules

English

Product Specifications

Application Specification

English

Agency Approvals

UL_EU_CERT_EN_61984_UL_EU_01778_M1_C1

English

CB_CERT_IEC_61984_US_34131_M1_UL_C1

English

CB_CERT_US_34131_M1_UL_4788988643_TR_C1

2343403-1

Shorting Cap, Black, Height 29.6 mm, Keyed / Not Vented, UL, 4 Position, Sealable, Power, -40 – 90 °C [-40 – 194 °F], LUMAWISE Endurance S



English