

**2347721-8**


✓ ACTIVE

**SFP56**

TE Internal #: 2347721-8

zSFP+ Stacked (SFP56), Cage Assembly with Integrated Connector,  
.6mm [.018in] Centerline, Signal[View on TE.com >](#)

Connectors &gt; Pluggable I/O Connectors &amp; Cages &gt; SFP56 Stacked Cage Assembly: EMI Spring

Form Factor: **zSFP+ Stacked (SFP56)**Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**Centerline (Pitch): **.6 mm [.018 in]**Circuit Application: **Signal**Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**[All SFP56 Stacked Cage Assembly: EMI Spring \(48\)](#)**Features****Termination Features**

Termination Method to PCB

Through Hole - Press-Fit

**Operation/Application**

Pluggable I/O Applications

SFP28

Circuit Application

Signal

**Product Type Features**

Cage Type

Stacked

Form Factor

zSFP+ Stacked (SFP56)

Pluggable I/O Product Type

Cage Assembly with Integrated Connector

**Configuration Features**

Number of Positions

20

Number of Ports

12

Port Matrix Configuration

2 x 6

**Electrical Characteristics**

Data Rate (Max)	56 Gb/s
-----------------	---------

### Housing Features

Centerline (Pitch)	.6 mm[.018 in]
--------------------	----------------

### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

### Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # 1761394-1  
DUST COVER, SFP, GANGED &  
STACKED


## Also in the Series | **SFP56**



Pluggable I/O Cable Assemblies(17)



Pluggable IO Connectors & Cages(53)




SFP, SFP+ & zSFP+(53)

## Customers Also Bought



TE Part #6-2213362-2  
RCPT ASSY,DIMMABLE  
PHOTOCONTROL,150C,3 P



TE Part #1734375-1  
CHAMP .050 HIGH RISE, REVERSED



TE Part #2132529-3  
IMP100S,H,V3P6C,LG,REW39,5.5



TE Part #5-1375870-4  
RCPT ASSY,12 POS,VERT,0.8MM MI




TE Part #1-1871058-5  
PCI EXPRESS CONN. EON TYPE,  
280P, L=3.25



TE Part #1734100-3  
Champ050 series,30pos,Au over PdNi



TE Part #1734101-3  
Champ050 series,30pos,Au over PdNi



TE Part #1757256-1  
SMPM FEMALE BULLET ADAPTER



## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2347721-8\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2347721-8\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2347721-8\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

#### [Application Specification](#)

English