


Connectors &gt; Terminal Blocks &amp; Strips &gt; Barrier Strips



Number of Positions: 10

Barrier Strip Style: Dual Barrier

Bottom Termination Type: Printed Circuit Pin

Connector System: Wire-to-Board

Centerline (Pitch): 9.53 mm [.375 in]

## Features

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Method	Package
------------------	---------

Packaging Quantity	100
--------------------	-----

### Operation/Application

Circuit Application	Power
---------------------	-------

### Mechanical Attachment

Top Termination Type	Wire Clamp Combo Head
----------------------	-----------------------

Mounting Options	None
------------------	------

Screw Plating Material	Zinc
------------------------	------

Screw Material	Steel
----------------	-------

Thread Size	6-32
-------------	------

Screw Head Type	Wire Clamp Combo Head
-----------------	-----------------------

Connector Mounting Type	Board Mount
-------------------------	-------------

### Contact Features

Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	20 A

### Dimensions

Product Length	96.8 mm[3.811 in]
Wire Size	22 – 12 AWG

### Housing Features

Housing Material	Polyamide
Centerline (Pitch)	9.53 mm[.375 in]

### Product Type Features

Block Style	Flat Bottom with standoffs
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

### Body Features

Terminal Profile	Low
Primary Product Color	Black
Product Orientation	Vertical
Barrier Strip Style	Dual Barrier

### Configuration Features

Number of Levels	1
Number of Positions	10
Number of Rows	1

### Termination Features

Bottom Termination Type	Printed Circuit Pin
-------------------------	---------------------

### Electrical Characteristics

Operating Voltage	300 V
-------------------	-------

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Other

EU RoHS Compliance	Compliant
--------------------	-----------

EU ELV Compliance

Compliant

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts





TE Part # 1-1437664-4  
NC6-P107-10=NC6 ASSEMBLY

## Also in the Series | Buchanan NC6



Barrier Strips(30)

## Customers Also Bought

TE Part #3-1393211-9  
T92P11A22-12TE Part #CAT-H3930-CH8172  
DEUTSCH HD30 HousingsTE Part #0413-003-1605  
SEALING PLUG, SIZE 16, BLUTE Part #350209-1  
02P CMNL HDR ASSY PC NATLTE Part #8-1437657-0  
8PCV-04-006-#8 TRIBARRIERTE Part #HDC36-24  
DUST CAP, 24SZ, REC, AL, LANYARD,  
HD30TE Part #112263-90  
PANEL NUT, SIZE 24, HD30TE Part #213647-1  
AMP PDS BUSPLUG 125F3 SERTE Part #5555003-1  
MJ,R/A,6P,PNL,RH LTCH,GRY

## Documents

### Product Drawings

#### NC6-P108-10=NC6 ASSEMBLY

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437664-4\\_M1.3d\\_stp.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437664-4\\_M1.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1437664-4\\_M1.3d\\_jgs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#)

English

[1-1773458-2\\_BARRIER\\_STRIPS\\_QUICK\\_REFERENCE\\_GUIDE](#)

English