

HC-B-G-M20-ER-AL - Cable gland

1411442

<https://www.phoenixcontact.com/us/products/1411442>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

EVO metal cable gland with bayonet locking, B series, size M20, cable diameter: 7 - 13 mm



Commercial data

Item number	1411442
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	BF7APM
Catalog page	Page 573 (C-4-2015)
GTIN	4046356932417
Weight per piece (including packing)	75.3 g
Weight per piece (excluding packing)	75.3 g
Customs tariff number	85389099
Country of origin	DE

HC-B-G-M20-ER-AL - Cable gland

1411442

<https://www.phoenixcontact.com/us/products/1411442>



Technical data

Product properties

Product type	Cable gland with bayonet locking
Application	for greater strain relief
No. of conductors	1
Type of the screw connection	M20
Shielded	no

Dimensions

Dimensional drawing	
Width	54 mm
Height	54.8 mm
Depth	54.8 mm
Wrench size, union nut	22 mm

Material specifications

Color	Aluminum color
Material Pressure screw	Brass, nickel-plated
Seal material O-ring	NBR
Seal material Cable seal	NBR
Housing material	Die-cast aluminum, corrosion resistant
Material for screw connection	Aluminum

Cable/line

External cable diameter Cable 1	9 mm ... 12 mm
---------------------------------	----------------

Mechanical properties

Mechanical data	
Type of the screw connection	M20

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C (static)

HC-B-G-M20-ER-AL - Cable gland


1411442

<https://www.phoenixcontact.com/us/products/1411442>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-G-M20-ER-AL - Cable gland

1411442

<https://www.phoenixcontact.com/us/products/1411442>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411442>

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

cULus Recognized

HC-B-G-M20-ER-AL - Cable gland

1411442

<https://www.phoenixcontact.com/us/products/1411442>



Classifications

ECLASS

ECLASS-11.0	27144432
ECLASS-12.0	27140801
ECLASS-13.0	27140801

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

HC-B-G-M20-ER-AL - Cable gland

1411442

<https://www.phoenixcontact.com/us/products/1411442>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7c5b99b5-eb4c-4303-9f22-51d94dd28480

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com