


Cable Assemblies > Data Bus Components > Data Bus Connectors

Data Bus Connector Type: **Plug**Data Bus Connector Style: **Threaded**Contact Type: **Pin**EU RoHS Compliance: **Not Compliant**EU ELV Compliance: **Not Compliant**

Features

Usage Conditions

Operating Temperature (Max)	125 °C
-----------------------------	--------

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Product Type Features

Data Bus Connector Type	Plug
-------------------------	------

Data Bus Connector Style	Threaded
--------------------------	----------

Contact Features

Contact Type	Pin
--------------	-----

Other

EU RoHS Compliance	Not Compliant
--------------------	---------------

EU ELV Compliance	Not Compliant
-------------------	---------------

Product Compliance

For compliance documentation, visit the product page on TE.com >

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC	Not Compliant
-----------------------------	---------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)
--	--

Candidate List Declared Against: JUNE

2024 (241)

SVHC > Threshold:

Pb (37% in Solder)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 750984-004
10612-24-9

Customers Also Bought



TE Part #806704-000
222A163-25-0




TE Part #E17344-000
CM-SCE-TP-1/2-4H-9



TE Part #696488-000
B-900-01



TE Part #610002-000
D-300-12



TE Part #6162-283-0877
CONT PIN ASSY



TE Part #024070-E
STVBUG E 160 CSI 172 9999 * J 4
24070 FE




TE Part #234063-E
STVROL BUT 500 CSI 2026 207 * AL J
2 340



TE Part #YDIV46E11-35SNC009
PLUG ASSY



TE Part #DS07-3S-059
PLUG ASSY



TE Part #6-1617039-3
HMS12104S01 = 2100 HMS RELAY

Documents

Product Drawings

[DK-621-0011-P](#)

English

Datasheets & Catalog Pages

[Data Bus Components Brochure](#)

English

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English