

KUEP-3D15-48

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield KUEP

TE Internal #: 1393114-2

General Purpose Power Relay, DC, Monostable, 1 Form X SPST-NO-DM, 10 A Contact Rating, 48 VDC Coil Voltage, Potter & Brumfield KUEP

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Current Type: **DC**

Coil Magnetic System: **Monostable**

Contact Arrangement: **1 Form X SPST-NO-DM**

Contact Current Rating: **10 A**

Features

Contact Features

Contact Material	AgCdO
------------------	-------

Dimensions

Product Width	35.71 mm[1.4 in]
Product Length	38.89 mm[1.53 in]
Product Height	48.41 mm[1.9 in]

Packaging Features

Packaging Method	Package
------------------	---------

Other

Coil Power Rating Class	1 – 1.5 W
Contact Current Class	16 A
Environmental Ambient Temperature Class	50 – 70 °C
Height Class (Mechanical)	40 – 50 mm
Length Class (Mechanical)	35 – 40 mm
Width Class (Mechanical)	30 – 40 mm
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant

Usage Conditions

Operating Temperature Range	-45 – 70 °C[-49 – 158 °F]
-----------------------------	---------------------------



Environmental Category of Protection	RTI
Environmental Ambient Temperature (Max)	70 °C[158 °F]

Body Features

Product Weight	85 g[2.988 oz]
Enclosure Type	Dust Protected

Electrical Characteristics

Contact Limiting Short-Time Current	10 A
Contact Limiting Making Current	10 A
Contact Limiting Continuous Current	10 A
Contact Limiting Breaking Current	10 A
Insulation Initial Dielectric Between Open Contacts	1200 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	2200 Vrms
Contact Switching Load (Min)	300mA @ 12V
Coil Resistance	1800 Ω
Insulation Initial Resistance	100 MΩ
Contact Current Rating	10 A
Coil Voltage Rating	48 VDC
Contact Voltage Rating	150 VDC
Coil Power Rating DC	1.3 W
Insulation Initial Dielectric Between Contacts & Coil	2200 Vrms

Configuration Features

Contact Special Features	Magnetic Blowout
Contact Number of Poles	1
Coil Special Features	UL Coil Insulation Class B
Contact Arrangement	1 Form X SPST-NO-DM

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Operation/Application

Current Type	DC
Coil Magnetic System	Monostable

Termination Features

Main Termination & Connection Type	Quick Connect Terminals
------------------------------------	-------------------------



Coil Termination & Connection Type

Quick Connect Terminals

Mechanical Attachment

Product Mount Type	Panel & Socket Mount
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>








EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Cadmium oxide (10% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts











			
TE Part # 1393143-2 27E067=SOCKET,KU,11,QC,187,NY	TE Part # 3-1393143-8 27E396=SOCKET,KU,11,SNAP,-,187QC	TE Part # 1393143-5 27E121=SOCKET,KUP,11,SCW,PLE	TE Part # 1393143-1 27E043=SOCKET,KU,11,SLG,NYL,N
			
TE Part # 1393114-4 KUEP-3D17-48=KU	TE Part # 1419106-4 27E046=SOCKET,KU,11,PC,NYL,NAT	TE Part # 2-1419106-5 27E893=SOCKET,KU,11,QC,POLY,NA-	


Also in the Series

Potter & Brumfield KUEP

			
AC Relays(2)	DC Relays(12)	Electromechanical Relays(14)	Plug-In Relays(14)

Customers Also Bought

			
TE Part #8-1393113-5 KUEP-11D15-110=KU	TE Part #6-1879627-0 H4P 3K0 1% 100PPM	TE Part #1SNK900001R0000 BAM4	TE Part #1SNA116538R1700 PC8-2
			
TE Part #1SNA116540R2500 PC8-4	TE Part #1SNA176791R2100 CPV4-5	TE Part #4-1393159-8 20C318=SPRING,HOLD-DOWN,K10,-0	TE Part #9-1393159-5 40G432=INSUL,SKT TRACK MTG,R10



Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1393114-2_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393114-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393114-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KUEP Series Relay Datasheet

English

KU Sockets & Accessories

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English