




SPLICE

TE Internal #: 1438254-1  
Splice Accessory, 0 Serration, Length 7.62 mm [.3 in], Strip, Open Barrel, Solid / Stranded Wire, Discrete Wire, Uninsulated, SPLICE  
[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: **Splice Accessory**  
Sealable: **No**  
Compatible Insulation Diameter Range: **5.97 mm [ .235 in ]**  
Terminal Material Thickness: **.51 mm [ .02 in ]**  
Number of Serrations: **0**

Features

Packaging Features

Packaging Quantity	15000
Packaging Method	Strip

Product Type Features

Splice Type	Splice Accessory
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Serrations	0
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Barrel Type	Open
-------------	------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Compatible Insulation Diameter Range	5.97 mm[.235 in]
Terminal Material Thickness	.51 mm[.02 in]
Product Length	7.62 mm[.3 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series

SPLICE

Crimp Wire Pins, Tabs & Ferrules(1)

Splices(63)

Customers Also Bought

TE Part #DT06-08SA-CE06  
PLG, 8P, GRY, E, SEAL RET, A

TE Part #CAT-H396-CH8172  
DEUTSCH HDP20 Housings

TE Part #9-2348795-1  
HD MATenet 1+12 REC HSG ASSY, GRP E

TE Part #2292863-3  
AS16,CAP BACKSHELL KIT,ST,06P, NC12

TE Part #2098633-1  
40P Shield Assy, GY LAC

TE Part #41276  
IDENTIFICATION BAND AL

TE Part #2386232-1  
REC CONN CVR ASSY,46POS,0.64 GENER. Y

TE Part #400-4301-4S  
SZ 4 LOCATOR

TE Part #8-1355512-6  
47 WAY ABS CONNECTOR

Documents

Product Drawings

ID BAND .020 AL

English

CAD Files

3D PDF

3D



Customer View Model

[ENG\\_CVM\\_CVM\\_1438254-1\\_D\\_c-1438254-1-d.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1438254-1\\_D\\_c-1438254-1-d.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1438254-1\\_D\\_c-1438254-1-d.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.