




Positive Lock | Positive Lock 250

TE Internal #: 926790-6

Quick Disconnect Receptacle, 17 – 13 AWG, 1.03 – 2.62 mm² Wire,
6.35 mm [.25 in] Tab Width, Flag, Brass, Tin Plating, Strip/Reel,
Positive Lock 250

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.03 – 2.62 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	.7 – 10.2 kgf

Packaging Features

Packaging Quantity	2000
Packaging Method	Strip/Reel

Dimensions



Compatible Insulation Diameter Range	3 – 4.3 mm[.118 – .169 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	1.03 – 2.62 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 926291-1
PL 250 HOUSING FLAG PA 6.6 BLACK

KIT
TE Part # 7-2150938-7
OCEAN_2.0_SPARE_PART_KIT-110F160F

TE Part # 2150938-2
OCEAN_2.0_Applicator-S-110F160F-SSA

Also in the Series | Positive Lock 250

Automotive Terminals(1)

Crimp Terminal Housings(184)

Insertion & Extraction Tools(3)

Insulation Boots & Sleeves(4)

Quick Disconnects(185)


Customers Also Bought



TE Part #1-967625-5
JUN-POW-TIM GEH 21P




TE Part #1-1415899-3
RZ03-1A4-D005




TE Part #1-1623789-8
SQM7 68R 5% (WIRE)



TE Part #1379217-1
5POS MIXED MQS REC COD Z



TE Part #1379218-1
COVER FOR 5W MPQ+MQS HSG



TE Part #1987984-1
AMP IN TERMINAL 11.5-10 AWG



TE Part #3-964951-2
STD TIMER GEH 2P



TE Part #3-1241961-7
STD TIM MK2 HSG 3P



TE Part #8-1415363-2
0430 45 280 100



TE Part #AS610-35PD
PLUG BOOT TERMIN'N TYPE 6

Documents

Product Drawings

PL 250 REC TERMINAL-FLAG 17-13 TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_926790-6_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926790-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_926790-6_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English