




Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**

Number of Positions: **6**

Centerline (Pitch): **2.5 mm [.098 in]**

Termination Method to Wire & Cable: **Insulation Displacement (IDC)**

Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	250 VAC, 50 VAC
-------------------	-----------------

Packaging Features

Packaging Quantity	8624
Packaging Method	Box

Dimensions

Compatible Insulation Diameter Range	1.2 – 1.6 mm [.047 – .063 in]
PCB Thickness (Recommended)	1.5 mm [.059 in]
Connector Height	7.3 mm [.287 in]
Wire Size	24 – 22 AWG

Mechanical Attachment

PCB Mount Retention	Without
Contact Retention Type Within Housing	Locking Lance
Mating Retention	Without
Mating Alignment Type	Keyed



Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Contact Features

Contact Retention Within Housing	With
Contact Mating Area Plating Material Thickness	3 – 6 µm
Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Tin
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Current Rating (Max)	2 A

Housing Features

Housing Entry Configuration	Both Ends Open
Centerline (Pitch)	2.5 mm [.098 in]
Housing Material	PA 6 GF

Configuration Features

Card Entry Style	Side
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	6
Number of Rows	1
Connector Contact Load Condition	Selectively Loaded
PCB Mount Orientation	Right Angle

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Natural
-----------------------	---------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------



Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Glow Wire Rating	GWEPT 750°C (Without Flame)
------------------	-----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1534798-6
AMP DUOPLUG MARK II




TE Part # 9-1534798-6
AMP DUOPLUG MARK II




TE Part # 5-1534798-9
AMP Duoplug 2,5 MK II selektiv



TE Part # 9-1740154-6
DUOPLUG MKII FEMALE HSG WITH PCB LOCKING



TE Part # 7-1534798-8
AMP DUOPLUG 2.5 MARK II FEMALE CONNECTOR



TE Part # 1-1534798-6
AMP DUOPLUG MARK II



TE Part # 4-1534798-5
AMP DUOPLUG MK2 CONNECTOR 5P SELECTIVE




TE Part # 3-1534798-9
AMP DUOPLUG MARK II CONNECTOR3-20P SELEC



TE Part # 4-1534798-0
AMP DUOPLUG MK II CON. 3-20 POS. SELECTIV

Customers Also Bought



TE Part #293041-2
FF 250 TAB 0.35-1.0MM2 TPBR



TE Part #3-1534796-6
AMP DUOPLUG MK2 CONNECTOR 6P



TE Part #3-1534796-4
AMP DUOPLUG MK2 CONNECTOR 4P S



TE Part #3-1534798-3
AMP DUOPLUG MK2 CONNECTOR 3P SELECTIVE



TE Part #2-1740918-3
AMP DUOPLUG2.5 MKII 3P W. PCB LOCK




TE Part #3-1534798-7
AMP DUOPLUG MK2 CONNECTOR 7P SELECTIVE



TE Part #1376477-4
2.5MM PITCH SIGNAL MATE CONN



TE Part #1534077-4
MULTIFITING MK2 ASSY,4POS



Documents

CAD Files

Customer View Model

ENG_CVM_CVM_5-1534798-6_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1534798-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1534798-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English

VDE Certificate

English