

T1270163140-000 ✓ ACTIVE

HDC | HDC IP65

TE Internal #: T1270163140-000

Heavy Duty Connector Hood, Side Entry, Locking, Sealable, HDC  
IP65

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

## Features

### Usage Conditions

Corrosion Protected	Yes
---------------------	-----

### Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

### Packaging Features

Packaging Method	Box
------------------	-----

### Dimensions

Product Width	43 mm
Product Length	93.5 mm
Product Height	76 mm

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Mechanical Attachment

Thread Size	M40
Locking Device Location	Hood
Hood & Base Locking Device Type	Locking

### Product Type Features

Hood & Base Connector Product Type	Hood
------------------------------------	------

Sealable	Yes
----------	-----

### Body Features

Cable Entry Location	Side
----------------------	------

### Other

EU RoHS Compliance	Compliant
--------------------	-----------

EU ELV Compliance	Compliant
-------------------	-----------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)
--	---

Candidate List Declared Against: JUNE  
2024 (241)

Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # T1420160000-000  
H16B-AG-BO



TE Part # T2040162101-000  
HE-016-M



TE Part # T3609400102-000  
DLX-40-M

## Also in the Series | **HDC IP65**



Rectangular Connector Hoods & Bases  
(1257)

## Customers Also Bought



TE Part #T2020082201-000  
HD-008-F



TE Part #1-480711-9  
15P UMNL CAP HSG BLK



TE Part #T2106062201-000  
HWK6/6-012-F



TE Part #640250-1  
01P SL156 HSG W/LCK RAMP NATL



TE Part #T0931003003-000  
CODING-PIN-M3



TE Part #1SNA195638R2300  
M4/6.4.P



TE Part #T1730060000-000  
H6B-TBF-T



TE Part #T2120100219-000  
ZGG-10DSTK,1-7,2-8,3-9,4-6,5-10



TE Part #T2120100220-000  
ZGGP-H10BSK 1-7/2-8/3-9/4-6/5-10



TE Part #1473203-1  
025 CAP ASSY 16P P/BACK BRCKT

## Documents

### Product Drawings

[H16B-TSBHS-M40](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T1270163140-000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1270163140-000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T1270163140-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

[HEAVY DUTY CONNECTORS](#)

Japanese

---

### Product Specifications

[Application Specification](#)

English