




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 42420 CMA

Stud Size: M6

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	19.4 g
----------------	--------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	25
Packaging Method	Box

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M6
Sealable	Yes
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Plating Material	Tin
Contact Underplating Material	None



Dimensions

Wire Size	42420 CMA
Stud Diameter	6.71 mm[.265 in]
Tongue Thickness	2.15 mm[.085 in]
Product Length	50.8 mm[1.99 in]
Barrel Inside Diameter	8.89 mm[.35 in]
Compatible Insulation Diameter (Max)	7.75 mm[.305 in]
Compatible Insulation Diameter Range	7.01 – 7.75 mm[.276 – .305 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1490557-1
HYP10 COPALUM SEALED 4AWG DIE SET

TE Part # 68008-1
DIE ASSY #4 SEALED COPALUM

Customers Also Bought

TE Part #4397130001
TMS-SCE-1-2.0-9

TE Part #YDTS26W25-35SNC001
PLUG ASSY

TE Part #290583-000
44A7422-4-1L

TE Part #490096-000
5012H3012-0

TE Part #290585-000
44A7422-6-1L

TE Part #238109-000
55PC2111-22-9-9CS2502

TE Part #CZ2482-000
55PC1226-22-2/6-9CS2502

TE Part #229623-000
82A0811-4-9-F874

TE Part #396777-000
82A0811-8-9-F874

TE Part #EJ3518-000
S200-2-55-20-9CS2904

Documents

Product Drawings
TERMINAL,COPALUM R 4 1/4
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_277149-2_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_277149-2_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_277149-2_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

COPALUM Lite Sealed Terminals and Splices

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English