



Connectors > Automotive Connectors > Automotive Housings > AMP Unsealed Connector Housing



Number of Positions: 6

Connector & Housing Type: **Housing for Male Terminals**

Mating Tab Width: **2.8 mm [.11 in]**

Connector System: **Wire-to-Board, Wire-to-Wire**

Centerline (Pitch): **5 mm [.197 in]**

[All AMP Unsealed Connector Housing \(110\)](#)

Features

Dimensions

Product Width	35.45 mm[1.396 in]
Product Length	17.5 mm[.689 in]
Connector Height	30.6 mm[1.205 in]

Packaging Features

Packaging Method	Box
Packaging Quantity	1500

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)



Other

Serviceable	No
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	28 VDC
Nominal Voltage Architecture	28 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Light Blue
Connector & Keying Code	C

Housing Features

Housing Material	PA GF
Centerline (Pitch)	5 mm[.197 in]

Contact Features

Contact Size	2.8mm
Contact Type	Tab
Mating Tab Width	2.8 mm[.11 in]

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Rows	2

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
-----------------------------	----------------



Operating Temperature Range

-40 – 120 °C[-40 – 248 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB




TE Part # 6-968970-1
AMP MCP 2.8 HSG 6POS 2.LOCKING

Also in the Series | AMP MCP 2.8



Automotive Connector Caps & Covers
(24)



Automotive Connector Locks &
Position Assurance(4)



Automotive Headers(32)



Automotive Housings(265)



Automotive Terminals(11)




Connector Seals & Cavity Plugs(5)




Insertion & Extraction Tools(13)



Module Components(1)



Other Automotive Connector
Accessories(2)




PCB Headers & Receptacles(32)

Also in the Series | **AMP MCP Connector System**




Automotive Connector Caps & Covers
(24)




Automotive Connector Locks &
Position Assurance(4)



Automotive Headers(32)



Automotive Housings(265)



Automotive Terminals(11)




Connector Seals & Cavity Plugs(5)




Insertion & Extraction Tools(13)



Other Automotive Connector
Accessories(2)



PCB Headers & Receptacles(32)




Wire-to-Board Headers & Receptacles (31)


Customers Also Bought



TE Part #338068-4
MICRO-MATCH FTE, 4P



TE Part #968271-1
2. KONT-SICHERUNG 6P




TE Part #1811957-1
ASY,SCRLESS WIRE CONN,VERT,2P




TE Part #CAT-AM705-CH8173
AMP Unsealed Connector Housing



TE Part #K1139190
Relay 29-114-11A



TE Part #2333679-1
MINI-FUSE RETAINER



TE Part #K1157198-4
Toggle Switch 07-2-2-10 939 CV750



TE Part #1-968875-2
AMP MCP 2.8, CONTACT SWS (LP)

Documents

Product Drawings

TAB HSG 2.8MM 6POS.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-965641-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-965641-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-965641-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



[Product Specifications](#)

[Application Specification](#)

English