




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Locking Lance Height	.93 mm
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	4000
Packaging Method	Strip/Reel

Dimensions

Product Length	21.5 mm[.846 in]
Compatible Insulation Diameter Range	2.2 – 3.4 mm[.086 – .134 in]



Terminal Material Thickness	.33 mm[.013 in]
Wire Size	.51 – 2.08 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 170303-1
FF 250 REC 22-18AWG BR WITH LATCH



TE Part # 2150034-1
OCEAN_2.0_APPLICATOR-E-110F180F-REM



TE Part # 2150034-2
OCEAN_2.0_APPLICATOR-E-110F180FA-REA




TE Part # 7-2150034-7
OCEAN_2.0_SPARE_PART_KIT-110F180F



TE Part # 2819183-1
.250 SERIES FASTIN FASTON REC.

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(207)



Insertion & Extraction Tools(2)




PCB Terminals(2)




Quick Disconnects(250)

Customers Also Bought




TE Part #2-521055-2
ULTRAFAST 250 ASSY TAB 22-18 AWG TPBR




TE Part #2-521144-2
ULTRA-FAST 250 ASY TAB 22-18 TPBR




TE Part #184032-1
3 POS. PLUG ASSY, KEY A



TE Part #350416-1
.093 COMM P&S PIN 14-20 PTPBR



TE Part #3-521191-2
ULTRA-FAST 250 ASY TAB 16-14 AWG TPBR



TE Part #583680-1
HSG AMP LEAF 15 POS



TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part #929937-3
JPT REC 2.8 Contact SWS Sn



TE Part #470037-000
CWT-9002

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-170031-2_AF.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-170031-2_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-170031-2_AF.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Crimping of 250 Series Tab and Receptacle Contacts

Japanese

Application Specification

Japanese



Application Specification

Japanese

Crimping of 250 Series Tab and Receptacle Contacts

Japanese