

Relays & Contactors > Electromechanical Relays

Relay & Contactor Type: **General Purpose Signal Relay**Current Type: **DC**Coil Magnetic System: **Non-Polarized, Monostable**Contact Arrangement: **2 Form C DPDT-CO**Contact Current Rating: **1 A**

Features

Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

Environmental Ambient Temperature (Max)	125 °C[257 °F]
---	----------------

Electrical Characteristics

Coil Resistance	1560 Ω
-----------------	--------

Contact Switching Voltage (Max)	28 VDC
---------------------------------	--------

Contact Current Rating	1 A
------------------------	-----

Coil Voltage Rating	26.5 VDC
---------------------	----------

Coil Power Rating DC	.45 W
----------------------	-------

Configuration Features

Coil Special Features	Coil Suppression Diode, Coil Polarity Protection Diode
-----------------------	--

Contact Arrangement	2 Form C DPDT-CO
---------------------	------------------

Operation/Application

Vibration Resistance	30G's, 10 – 3000Hz
----------------------	--------------------

Shock Resistance	75G's, 6ms
------------------	------------

Current Type	DC
--------------	----

Coil Magnetic System	Non-Polarized, Monostable
----------------------	---------------------------

Product Type Features

Relay & Contactor Type

General Purpose Signal Relay

Body Features

Enclosure Type

Hermetically Sealed

Termination Features

Main Termination & Connection Type

Extended Leads

Coil Termination & Connection Type

Extended Leads

Mechanical Attachment

Product Mount Type

Board Mount

Other

EU RoHS Compliance

Compliant

EU ELV Compliance

Not Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://te.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024
(241)Candidate List Declared Against: JAN 2024
(240)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per
homogenous material. Also BFR/CFR/PVC
Free

Solder Process Capability

Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2-1617031-1
HFW1201K45M = M39016/6-109M

Customers Also Bought



TE Part #1623793-3
SQP5 1K0 5% MTL FLM



TE Part #4-1617758-7
FCB-205-0222M=M83536/2-022M



TE Part #212447-2
SCREW RTNR KIT,AMPLIMITE



TE Part #5748677-4
PLTD PLST CBL CLMP KIT,SZ 4



TE Part #CONSMA012-R178
SMA Plug 50 Ohm Cable Crimp



TE Part #5-2176331-6
CRGP 2512 390K 1%



TE Part #1589467-8
SSM005L82AQ = SMT Conn



TE Part #5-1617791-0
FCA-125-3701L=M83536/37-001L



TE Part #2-1617031-3
HFW1201K46 = M39016/6-209L



TE Part #3-1617752-9
FCA-215-BY4

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1617148-4_J.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617148-4_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617148-4_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec1_MGA](#)

English

RELAY

English