




EMI & EMC Solutions > EMI Filters > Power Line Filters > Single Phase Filters > Single Phase Filters, Corcom HT Series



Current Rating: 10 A

Input Termination Type: Wire Lead

Output Termination Type: Wire Lead

Leakage Current (Max) (120VAC, 60Hz): .002 mA

Leakage Current (Max) (250VAC, 50Hz): .005 mA

[All Single Phase Filters, Corcom HT Series \(9\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Type Features

Filtering Requirements	Filtered
Ground Choke Option	No
Input Termination Type	Wire Lead
Output Termination Type	Wire Lead

Electrical Characteristics

Current Rating	10 A
Leakage Current (Max) (120VAC, 60Hz)	.002 mA
Leakage Current (Max) (250VAC, 50Hz)	.005 mA
Operating Voltage	250 VAC



Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-H857
Single Phase Filters, Corcom HQ Series



TE Part # CAT-C8114-H85999
Single Phase Filters, Corcom HT Series

Also in the Series | Corcom HT



Single Phase Filters(9)

Customers Also Bought



TE Part #2-6609006-3
6EJT1=F8135



TE Part #8-34541-1
PIDG SPD 22-16COMM 22-18MIL 6



TE Part #8-320665-1
PG SPD 22-16 COMM 22-18 MIL 6




TE Part #2-1437667-4
4DB-P108-02=4DB ASSEMBLY



TE Part #34109
SOLIS R 22-16 COMM 22-18MIL 10



TE Part #60465-2
250 FASTON TAB TPBR



TE Part #2-520184-2
ULTRAFAST 250 ASSY REC 22-18
TPBR LP



TE Part #8-1393239-4
RT314F03



TE Part #2-34161-1
TERMINAL,PG R 16-14 10



TE Part #328377
TERMINAL,SOLIS R 16-14 2

Documents

Product Drawings
10EHT3=F7668 S0

English

CAD Files
Customer View Model
ENG_CVM_CVM_1-6609053-0_A1.3d_igs.zip

English

Customer View Model



[ENG_CVM_CVM_1-6609053-0_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609053-0_A1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_HT_SERIES](#)

English

Corcom Combined Selector Charts

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English