



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Interface Seal**
Primary Product Material: **Silicone Foam**
Primary Product Color: **Black**
Operating Temperature (Max): **105 °C [221 °F]**
Number of Positions: **2**

Features

Housing Features

Centerline (Pitch)	6.35 mm[.250 in]
--------------------	------------------

Packaging Features

Packaging Method	Reel
Packaging Quantity	1000

Product Type Features

Connector Seal & Plug Type	Interface Seal
----------------------------	----------------

Body Features

Primary Product Material	Silicone Foam
Primary Product Color	Black

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Configuration Features

Number of Positions	2
---------------------	---



Other

EU RoHS Compliance	Compliant
--------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 350986-4
02P UMNL HDR ASSY LNG/TL



TE Part # 350824-4
02P UMNL HDR ASSY PC LF



TE Part # 350777-1
02P UMNL PLUG HSG



TE Part # 350831-1
02P UMNL HDR ASSY PC 94VO



TE Part # 350786-1
02P UMNL HDR ASSY 94VO



TE Part # 350787-1
02P UMNL PIN HDR ASSY 94VO



TE Part # 2029383-1
06P UMNL-II FRONT2RR FOAM SPCR



TE Part # 350428-4
02P UMNL PIN HDR ASSY NATL AU



TE Part # 350582-4
02P UMNL PIN HDR ASSY V2 LF



TE Part # 350759-4
02P UMNL HDR ASSY PC V2 NATL



TE Part # 641963-3
02P UMNL PIN HDR ASSY POL LF



TE Part # 641964-3
02P UMNL PIN HDR ASSY POL LF



TE Part # 1-480699-0
02P UMNL CAP HSG NATL




TE Part # 350787-3
02P UMNL PIN HDR ASSY 94VO LF



TE Part # 641963-1
02P UMNL PIN HDR ASSY POL NATL



TE Part # 350778-1
02P UMNL CAP HSG



TE Part # 1-480698-0
02P UMNL PLUG HSG NATL



TE Part # 1-350942-0
02P UMNL HDR ASSY R/A 94VO



TE Part # 350428-1
02P UMNL PIN HDR ASSY NATL



TE Part # 3-350942-0
02P UMNL HDR ASSY R/A 94VO LF

Also in the Series | [Universal MATE-N-LOK](#)



Connector Caps & Covers(34)



Connector Contacts(209)



Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)



Insertion & Extraction Tools(4)



PCB Headers & Receptacles(284)




Power Contacts(209)



Wire-to-Board Headers & Receptacles (284)

Customers Also Bought



TE Part #1-520935-2
PL 250 HOUSING REC RED 6/6
NYLON V2



TE Part #794761-1
09P UMNL CAP HSG WHITE,P/MT,V0



TE Part #1586851-1
02P UMNL PLUG HSG, GW



TE Part #63127-1
250 FASTON REC 22-18 AWG BR



TE Part #350699-1
UMNL SPLIT PIN PTPBR



TE Part #1586856-1
02P UMNL CAP HSG, GW



TE Part #5-177901-1
POWER DBL LOCK PLUG HSG 6P
(GWT)



TE Part #647662-1
EP CONN CONT LUBRICANT SPCL



TE Part #3-647449-1
SL156 RCPT,SPCL LUBE, LF



TE Part #60650-1
250 FASTON FLAG REC 18-14 AWG
BR

Documents

Product Drawings

02P UMNL BLACK INTERFACE SEAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_794991-1_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_794991-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794991-1_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_794991-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_794991-1_E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_794991-1_E.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English