


M8 Connector

TE Internal #: T4030014041-000

4 Position Circular Connector, Wire-to-Panel, Sealable, Wire & Cable, Signal, Panel Mount, Reverse Gender, Nickel, Copper Alloy, Code A, M8 Connector

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M8 Panel Mount Solder Cups



Number of Positions: 4

Connector System: **Wire-to-Panel**Sealable: **Yes**Connector & Contact Terminates To: **Wire & Cable**Contact Current Rating (Max): **3 A**[All M8 Panel Mount Solder Cups \(8\)](#)**Features****Electrical Characteristics**

Operating Voltage	30 VAC
-------------------	--------

Packaging Features

Packaging Quantity	1
--------------------	---

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Usage Conditions

IP Dust Sealing Level	6
-----------------------	---

IP Water Sealing Level	IP67
------------------------	------

Operating Temperature Range	-40 – 85 °C [-40 – 185 °F]
-----------------------------	----------------------------

Body Features

O-Ring Material	Silicone
Environmental Protection	IP67
Environmental Protection Type	Sealed
Primary Product Color	Black
Peripheral Seal Material	Silicone
Shell Plating Material	Nickel
Shell Base Material	Copper Alloy
Circular Connector Insulation Material Type	Polyamide 67 GF30
Hermetically Sealed	Yes

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Mating Alignment	With
Connector Mounting Type	Panel Mount
Polarization Code	A
Mating Alignment Type	Keyed

Product Type Features

Assembly Requirement	Factory Assembled
Circular Connector Shell Type	Metal-Shell
Connector Product Type	Connector Assembly
Assembly Type	Electrical Connector
Connector System	Wire-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	No
Number of Positions	4
Number of Power Positions	0
Number of Signal Positions	4
Contacts Preloaded	Yes

Contact Features

Contact Current Rating (Max)	3 A
Reverse Gender	Yes
Circular Connector Contact Type	Pin

Housing Features

Circular Connector Shell Size	12.6
-------------------------------	------

Dimensions

Wire Size	18 – 24 AWG
-----------	-------------

Operation/Application

Circuit Application	Signal
Shielded	No

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # T4010008041-000
M8,SCREW, FEMALE,S,UNSHIELD,4P,
GOLD


Also in the Series | M8 Connector



Connector Hardware(4)



M8/M12 Cable Assemblies(147)




Standard Circular Connectors(106)

Customers Also Bought



TE Part #T4110002031-000
M12,FEMALE,STRAIGHT,A CODE,3P,
PG9,GOLD



TE Part #1658612-2
25 POS HDF RCPT, MS, LEAD FREE



TE Part #CAT-C73765-M1G
M12 Panel Mount Solder Cups



TE Part #T4012008041-000
M8,SCREW, FEMALE,R/A,UNSHIELD,
4P,GOLD



TE Part #2013595-1
INDUSTRIAL MINI I/O PLUG KIT D1



TE Part #T4061420004-005
M8 CABLE RA FEMALE 5M 4POS PUR
CABLE



TE Part #T4142012081-000
M12,FRONT MOUNT,MALE,A,8P,
SOLDER PCB



TE Part #747275-2
025 LP HDF STRAIN RELIEF



TE Part #182649-1
17-14 CPC PLUG RS

Documents

Product Drawings

[M8.MLE.PNLREAR.4POS.STR.](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T4030014041-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4030014041-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4030014041-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

Agency Approvals

[UL](#)

English