

TE Internal #: BEA088N00000222000

Cable-to-Panel, Power, Panel Mount, Electrodeposited Nickel, Zinc Alloy, PA66, Shell Size 23, Shielded, Receptacle, Metal, -20 – 130 °C [-4 – 266 °F]

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors

Connector System: **Cable-to-Panel**Sealable: **No**Circuit Application: **Power**Connector Mounting Type: **Panel Mount**Shell Plating Material: **Electrodeposited Nickel**

Features

Electrical Characteristics

Operating Voltage	630 VDC
-------------------	---------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Compatible With Approved Standards Products	UL
---	----

Body Features

Environmental Protection	IP67
--------------------------	------

Shell Plating Material	Electrodeposited Nickel
------------------------	-------------------------

Shell Base Material	Zinc Alloy
---------------------	------------

Circular Connector Insulation Material Type	PA66
---	------

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
--------------------------	----------------------------

Mating Retention Type	Speedtec (Triple Start Threaded)
-----------------------	----------------------------------

Connector Mounting Type	Panel Mount
-------------------------	-------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Power
Shielded	Yes

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Panel
Sealable	No
Circular Connector Type	Receptacle
Shell Type	Metal

Housing Features

Circular Connector Shell Size	23
-------------------------------	----

Usage Conditions

Operating Temperature Range	-20 – 130 °C [-4 – 266 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3% in Component)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # C0-0201-000-P00
CRIMPING TOOL MID-SIZE



TE Part # C0-0236-000-P00
DIGITAL CRIMPING TOOL, MID SIZE



TE Part # C0-0004-000-000
POSITIONING INSERT FOR 2 MM
CONTACTS



TE Part # BSA085N00420235000
923 PLUG



TE Part # BSA085N00420235000
923 PLUG


Customers Also Bought



TE Part #10-0388-002-000
940 PLUG HOUSING



TE Part #10-0389-002-000
940 PLUG HOUSING



TE Part #40-0623-000-000
623 INSULATION INSERT, 17-PIN



TE Part #BGC110M11001223000
923 RECEPTACLE, ANGLED,
ROTATABLE



TE Part #BGC898N0000157A000
917 RECEPTACLE, ANGLED,
ROTATABLE



TE Part #1-1106100-1
SPB-M3

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_BEA088N00000222000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_BEA088N00000222000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_BEA088N00000222000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BEA088N00000222000](#)

English

[fuer Datenblaetter, die online konfigurierbar sind](#)

German

[923 Einbaudose IG3 mit Montagegewinde, 6-polig BEGA088NN00000222000 DE-EN - Umstellungshinweiss](#)

German

Product Specifications

German