




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**

Primary Product Material: **Thermoplastic**

Primary Product Color: **Gray**

Compatible With Connector Shell Size: **1**

Shielded: **Yes**

Features

Dimensions

Compatible Insulation Diameter Range	4 – 8 mm[.158 – .315 in]
--------------------------------------	--------------------------

Housing Features

Compatible With Connector Shape	D-Shaped
Body Orientation	Straight

Body Features

Primary Product Plating Material	Nickel over Copper
Cable Exit Angle	37.5°
Primary Product Material	Thermoplastic
Primary Product Color	Gray

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Operation/Application

Compatible With Connector Shell Size	1
Shielded	Yes



Configuration Features

Number of Positions	9
---------------------	---

Mechanical Attachment

Thread Size	14702
-------------	-------

Packaging Features

Packaging Method	Box
Packaging Quantity	200

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Perfluorobutane sulfonic acid (PFBS) and its salts (.16% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 5-1393738-3
[V42254A6002K109M=SUB D GEHAEUS](#)


Customers Also Bought




TE Part #259472-000
[202K132-25-01/225-0](#)




TE Part #1658681-1
[HDP-22,RCPT,SIZE 1,15 POSN](#)




TE Part #167293-1
[15P.HDP20 PLUG ASSY](#)




TE Part #1478763-9
[METAL BACKSHELL 9 WAY 45 DE](#)




TE Part #626617-000
[222K132-100/86-0](#)




TE Part #480093-000
[342A012-100/86-0](#)




TE Part #TCD14741111-003
[M12D4-MS-RJ-PVC-22SH-TYPE B GREEN-1.5M](#)



TE Part #D475533001
[VG-95218-T020-E109](#)



TE Part #8656413001
[VG-95218-T023-F002](#)



TE Part #3267153001
[VG-95218-T021-E003](#)

Documents

Product Drawings
[V42254A6004G109=SUB D GEHAEUSE](#)
English



CAD Files

Customer View Model

ENG_CVM_CVM_5-1393738-9_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1393738-9_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_5-1393738-9_B1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

mounting guideline for d-Sub housings

English

Instruction Sheet (U.S.)

English