




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Gland**

Sealable: **Yes**

EU RoHS Compliance: **Compliant with Exemptions**

EU ELV Compliance: **Compliant with Exemptions**

Features

Product Type Features

Strain Relief Accessory Type	Cable Gland
Sealable	Yes

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (3.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # T1360062120-000
H6B-TGB-M20



TE Part # T1190102032-000
H10B-TGH/TSH-M32/2M20



TE Part # T3161200050-000
LN-20-M



TE Part # T1220100120-000
H10B-TG-M20



TE Part # T3165200111-000
BLIND-20-M

Customers Also Bought



TE Part #2-2299960-1
TRAY PACKAGE.THERMOCOUPLE
CONN KTYPE TAB



TE Part #T1210100120-000
H10B-TS-M20



TE Part #T1410100000-000
H10B-AG-SL



TE Part #T3609400102-000
DLX-40-M



TE Part #2-1903130-0
DYNAMIC 1200D TAB HSG 20P F/H
BLACK Y

TE Part #1-170823-5
250 FASTON SLEEVE,REC.,
TRANSPARENT

TE Part #2312733-2
HMN-HD3-10-M

TE Part #T2070104101-002
H10BN-T3-M-HD

TE Part #T2070104201-002
H10BN-T3-F-HD

TE Part #T2070244101-002
H24BN-T6-M-HD

Documents

Product Drawings

DLX-20-MT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T3609200112-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T3609200112-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T3609200112-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications



Application Specification

English