




Terminals & Splices > Splices



Splice Type: **Pigtail Splice**
Wire Size: **.3 – 1.5 mm²**
Sealable: **No**
Splice Capacity: **3**

Features

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Termination Features

Crimp Width	2.79 mm[.11 in]
-------------	-----------------

Packaging Features

Packaging Quantity	30000
Packaging Method	Strip

Contact Features

Terminal Plating Material	Tin
Contact Base Material	Phosphor Bronze
Barrel Type	Open

Configuration Features

Strip Orientation	End Feed
Splice Capacity	3
Number of Serrations	9



Product Type Features

Splice Type	Pigtail Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Magnet Wire

Body Features

Splice Features	Serrated
-----------------	----------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	600 – 3000 CMA
Terminal Material Thickness	.41 mm[.016 in]
Product Length	5.72 mm[.225 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC






Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2161800-2 APT-5A TERMINATING MACHINE	 TE Part # 1-2161900-2 APT-5E TERMINATING MACHINE	 TE Part # 2150117-2 OCEAN-2.0-APPLICATOR-E-110F-SEA	 TE Part # 1-2217700-2 APT 5E HF
 TE Part # 1-2217600-2 APT-5A HF	 TE Part # 1-2217600-6 APT-5A HF	 TE Part # 1-2161900-6 APT 5E	 TE Part # 7-2150117-7 OCEAN_2.0_SPARE_PART_KIT-110F
 TE Part # 1-2161800-6 APT 5A	 TE Part # 1-2326143-2 RETROFIT KIT, INFINITE SPLICE	 TE Part # 1-2217700-6 APT 5E HF	 TE Part # 1-2326145-2 APT-5E INFINITE SPLICE



Also in the Series | AMPLIVAR



Customers Also Bought





TE Part #E31096-000

LSTT-R-KIT-1



TE Part #4-1415540-5

XT4S4LC4

Documents

Product Drawings

AMVAR SPLC 600-3000 016TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62305-3_N_c-62305-3-n.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_62305-3_N_c-62305-3-n.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_62305-3_N_c-62305-3-n.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English