

1-2308345-7 ✓ ACTIVE

Rail D-Sub Backshells

TE Internal #: 1-2308345-7

Shielded, Backshell, Zinc, Straight, Shell Size 4, 37 / 62 Position,
Crimp Ferrule Termination, Rail D-Sub Backshells

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Backshells > D-SUB BACKSHELL SIZE 4



Connector Backshell Product Style: **Shielded**

Connector Backshell Product Type: **Backshell**

Primary Product Material: **Zinc**

Body Orientation: **Straight**

Compatible With Connector Shell Size: **4**

[All D-SUB BACKSHELL SIZE 4 \(8\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Mechanical Attachment

Mating Retention Type	Jackscrew
Thread Size	4-40 UNC

Body Features

Cable Exit Angle	180°, 45°
Primary Product Material	Zinc

Product Type Features

Connector Backshell Product Style	Shielded
Connector Backshell Product Type	Backshell
Sealable	No
Termination Device Type	Crimp Ferrule

Housing Features

Body Orientation	Straight
Compatible With Connector Shape	D-Shaped

Operation/Application

Compatible With Connector Shell Size

4

Configuration Features

Number of Positions

37, 62

Usage Conditions

Operating Temperature Range

-40 – 90 °C [-40 – 194 °F]

Other

EU RoHS Compliance

Compliant with Exemptions

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024
(241)Candidate List Declared Against: JAN 2024
(240)SVHC > Threshold:
Pb (3.5% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 1-2308348-8
CRIMP FLANGE 8 LARGE


Also in the Series | Rail D-Sub Backshells




Connector Backshells(55)



Connector Contacts(5)




Connector Hardware(19)



Connector Strain Relief(67)




Crimp D-Sub Connectors(10)



Insertion & Extraction Tools(2)

Customers Also Bought

TE Part #6648434-1
CONTACT,SKT,SIZE 1/4 (712-81-01107)TE Part #966067-4
FER, WIRE, PL SLV, .75/18, L6, GREY, LPTE Part #34856
TERMINAL,PG R 12-10 5/16TE Part #52955-1
TERMINAL,PG SPR SPD 16-14 6TE Part #31181
TERMINAL,BODY FLAG R 16-14 10TE Part #1-1423673-4
W51-A122B1-20=CKTBKR,THERM,ROCTE Part #1-2308319-1
FULL METAL HOODS SIZE 1 (1)TE Part #TRA6927M3NB-001
OMNI,Ph,NMO,698/1710 MHz BK,3
dBi,100W



Documents

Product Drawings

FULL METAL HOODS SIZE 4 - 7 (RAW)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-2308345-7_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2308345-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2308345-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Rail D-Sub Backshells Flyer

English