




Connectors > D-Shaped Connectors > D-Sub Connectors > Crimp D-Sub Connectors



Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **25**

Connector Shell Size: **3**

Shielded: **No**

Features

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Contact Features

Contact Options	Order Separately
-----------------	------------------

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Connector Shell Size	3
Sealable	No

Configuration Features

Number of Positions	25
---------------------	----

Operation/Application

Shielded	No
----------	----

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Customers Also Bought



TE Part #6609987-2  
15SRB1-R=F8219A



TE Part #205555-2  
AMPLIMITE,ASY,RCPT,STD,109,1



TE Part #5748676-2  
DIE CAST CBL CLMP KIT,SZ 2



TE Part #1-322249-0  
PG SPD FLG 22-16COMM22-18MIL 8



TE Part #7-1393254-4  
W92-X112-25=M6/M7/M9/W6/W7




TE Part #3-1393247-6  
W31-X2M1G-25=W23/W31




TE Part #747844-4  
09 MSFL RCPT RA 318 (IN,FM,BL)



TE Part #YDTS26W19-35PNV001  
PLUG ASSY



TE Part #1-102536-1  
26 AMPMODU MT COVER DR .100CL



TE Part #Y22628-10-6PC03300  
HERM RECP

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_747553-3\_G.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_747553-3\_G.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_747553-3\_G.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.