




PIDG

TE Internal #: 31880

Closed Ring Tongue Terminal, 22 AWG, #4 / M2.5 Stud, 3.02 mm [.119 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially Insulated, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 509 – 3260 CMA

Stud Size: M2.5, #4

[All PIDG Ring Tongue Terminals \(410\)](#)

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	Yes
-------------------------------	-----

Body Features

Product Weight	.637 g
Insulation Sleeve Color	Red
Stripe Color	Red

Packaging Features

Packaging Quantity	1000
--------------------	------

Packaging Method

Loose Piece

Contact Features

Military Part Class	Class I
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M2.5, #4
Wire Insulation Support Retention Type	Insulation Support

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	3.02 mm [.119 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	17.07 mm [.672 in]
Compatible Insulation Diameter (Max)	3.56 mm [.14 in]
Compatible Insulation Diameter Range	2.67 – 3.56 mm [.105 – .14 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 169400
CERTI-LOK FRAME W/O DIES



TE Part # 59250
T-HEAD PIDG 26-14 ASSY



TE Part # 2392021-1
RED BATTERY DAHT KIT 110V (47689-4)




TE Part # 539691-2
ERGO DIE R.B.Y



TE Part # 169404
CERTI-LOK DIE



TE Part # 2063030-1
SDE DIESET, RBY, UL



TE Part # 2392021-2
RED BATTERY DAHT KIT 220V (47689-4)



TE Part # 47806-2
DIES PIDG 22-16 DIE SET



TE Part # 58423-1
DIE, RBY IS9252



TE Part # 47386
DAHT PG PIDG 26-16 ASSY



TE Part # 58433-3
PRO CR ASSY, RBY IS9252



TE Part # 47386-4
DAHT PG PIDG 26-16 ASSY



TE Part # 59300
T-HEAD PIDG PG 26-16 ASSY




TE Part # 525690
DAHT PG PIDG 20-18 ASSY



TE Part # 59824-1
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY


Also in the Series | PIDG




Compression Connectors(17)




Crimp Wire Pins, Tabs & Ferrules(41)




Knife Disconnects(11)




Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(41)

Customers Also Bought



TE Part #31888
PIDG R 22-16 COMM 22-18 MIL 8



TE Part #6-192038-0
LA3 .280, .008, SILVER PL



TE Part #1623933-3
CFR50 5% 330K



TE Part #5-1617536-7
HFW1230L01=M39016/6-133L





TE Part #5-1616970-9
K200A1C=CONTACTOR 200 AMP
SPST 28 VDC



TE Part #D369-P33-NP1
369 3 WAY PLUG, CRIMP, PIN



TE Part #1-1414632-0
V23132B2002X025



TE Part #ZPF000000000123107
FDBA 56-20-16 PW-K-A5357



TE Part #D369-STB-3
369 3 WAY BACKSHELL STRAIGHT
TIE WRAP

TE Part #1-1616992-7
K500A1C=CONTACTOR SPST NO DB
500 AMP

Documents

Product Drawings

PIDG R 22-16 COMM 22-18 MIL 4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_31880_AA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_31880_AA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_31880_AA.3d_stp.zip

English

Customer View Model

ENG_CVM_31880_T.3d_igs.zip

English

Customer View Model

ENG_CVM_31880_T.3d_stp.zip

English

Customer View Model

ENG_CVM_31880_T.2d_dxf.zip

English

3D PDF

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
PIDG TERMINALS & SPLICES Quick Reference Guide
English

Instruction Sheets
Instruction Sheet (U.S.)
English

Agency Approvals
UL Report
English