



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp Kit**
Primary Product Material: **Thermoplastic**
Primary Product Color: **Black**
Compatible With Connector Shell Size: **11**
Cable Entry Diameter: **12 mm [.453 in]**

Features

Housing Features

Compatible With Connector Shape	Circular
Body Orientation	Straight

Product Type Features

Strain Relief Accessory Type	Cable Clamp Kit
------------------------------	-----------------

Body Features

Primary Product Material	Thermoplastic
Primary Product Color	Black

Operation/Application

Compatible With Connector Shell Size	11
Shielded	No

Dimensions

Cable Entry Diameter	12 mm[.453 in]
----------------------	----------------

Mechanical Attachment

Thread Size	1/2-20 UNEF-2B
-------------	----------------



Packaging Features

Packaging Method	Individual
Packaging Quantity	1

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1445817-1
PLUG,11-8,SM INS,STD KEY

Also in the Series | AMP CPC



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Contacts(6)



Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)




Insertion & Extraction Tools(1)




Power Contacts(6)


Customers Also Bought




TE Part #1445816-1
RECPT,11-9,FLNG MT,STD KEY




TE Part #759025-000
7824E0422-9X



TE Part #1445824-3
REC,11-5,FLNG MT,LG INS,STD KE



TE Part #32861
TERMINAL,DG R 26-22 6



TE Part #167300-6
MOD-4 REC.CONTACT



TE Part #1445819-1
PLUG,11-6,SM INS,STD KEY



TE Part #EC0054-000
05801914



TE Part #1437720-6
T01-0580-S07-FEMALE REC PANEL
MNT SOLDER



Documents

Product Drawings

STR RELIEF ASY,STRAIGHT SZ 11

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1445856-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_1445856-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_1445856-1_A.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1445856-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1445856-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1445856-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773902-9_CPC_Catalog

English

1-1773902-9_CPC_Catalog

1-1773902-9_CPC_Catalog

German



1-1773902-9_CPC_Catalog

Japanese

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

Product Specifications

Application Specification

English