




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab & Receptacle**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
---	---------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Multiple

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Packaging Features

Packaging Quantity	3500
Packaging Method	Strip/Reel

Dimensions

Product Length	15.62 mm[.615 in]
----------------	-------------------



Compatible Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]
Terminal Material Thickness	.36 mm[.014 in]
Wire Size	.32 – .82 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Tab & Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Piggyback
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2266078-1
[OCEAN_2.0_Applicator-S-070F1400-RSM](#)

KIT
TE Part # 7-2266078-7
[OCEAN_2.0_SPARE_PART_KIT-070F1400](#)

TE Part # 2266078-2
[OCEAN_2.0_Applicator-S-070F1400-RSA](#)

TE Part # 2305570-1
[Strip Terminal Cutter-Side Feed-No Crimp](#)

Also in the Series | **FASTON 187**

[Crimp Terminal Housings\(41\)](#)

[Insertion & Extraction Tools\(1\)](#)

[Joints & Splices\(1\)](#)

[PCB Terminals\(42\)](#)

[Quick Disconnects\(207\)](#)

[Splices\(1\)](#)

Customers Also Bought



TE Part #770849-3
03P SL156 HSG W/LCK RMP & TABS

TE Part #D07339-000
HW-191064-10-9

TE Part #GA10K3A1A
DISCRETE 10K OHMS, +/-0.1C FROM 0C TO 70C

TE Part #2-520401-2
ULTRA-FAST 187 ASY REC 22-18 TPBR

TE Part #640254-1
KEYING PLUG .045 SQ PST CONN

TE Part #1217345-1
110 FASTON, REC., 16-18 AWG, BR

TE Part #647344-7
07P SL156 HSG W/RP TB BLK #3

TE Part #3-520106-2
ULTRA-FAST 250 ASY TAB 16-14 AWG TPBR

TE Part #GPSU15M
GPO, STD, 1.5GHz NMO, 26

TE Part #1-521204-6
HSG, POS LOCK, .250 SERIES, 2 POSITION

Documents

Product Drawings

FASTON 187 PIGGY-BACK REC 22-18 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1217084-1_F_c-1217084-1-f.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1217084-1_F_c-1217084-1-f.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1217084-1_F_c-1217084-1-f.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Application Specification

English