



TE Internal #: 413524-5
BNC Connector, Jack, 50 ohm, Bayonet, 1 GHz, Cable-to-Board, 1
Position, Printed Circuit Board, Panel Mount, -55 – 85 °C [-67 – 185 °
F], Zinc, Nickel
[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: **BNC**
RF Connector Style: **Jack**
RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**
Impedance: **50 Ω**
RF Connector Coupling Mechanism: **Bayonet**

Features

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	4 mm[.157 in]

Other

Grade	Commercial
Dielectric Material	Polymethylpentene
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant

Contact Features

RF Connector Center Contact Underplating Material	Nickel
	889 μin
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Phosphor Bronze

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------



Operating Temperature Range

-55 – 85 °C[-67 – 185 °F]

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	1
Number of Coaxial Contacts	1

Mechanical Attachment

Panel Mount Feature Type	Lockwasher and Nut
PCB Mount Retention	With
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

Mounting Post Length	2.79 mm[.11 in]
Profile Height from PCB	15.88 mm[.625 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Electrical Characteristics

Impedance	50 Ω
-----------	------

Operation/Application

Operating Frequency	1 GHz
---------------------	-------

Body Features

Body Material	Zinc
Body Plating Material	Nickel

Packaging Features

Packaging Method	Tube
------------------	------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5330876
BNC PLUG



TE Part # 5221128-1
PLUG,COMMERCIAL BNC



TE Part # 2-221128-3
PLUG,COMMERCIAL BNC



TE Part # 5227426-1
BNC BLKHD RECPT SEALED





TE Part # 5413959-3

[BNC HEX RT ANG PLUG 50 OHM](#)



TE Part # 2-5221128-3


[PLUG,COMMERCIAL BNC](#)



TE Part # 1-221128-0


[PLUG,COMMERCIAL BNC](#)

Customers Also Bought



TE Part #1-2199298-6

[20P,DIP SKT,300 CL,LDR,PB FREE](#)



TE Part #3-1461491-6

[PCN-124D3MHZ,000](#)



TE Part #5745174-1

[CABLE CLAMP KIT,SZ 4](#)



TE Part #8-1393243-2

[RT425012](#)



TE Part #103946-1

[8X2 MTE SHRD PIN SR POL .100CL](#)




TE Part #2176513-9

[CJP 1000W 10R 5% Lead](#)



TE Part #91523-1

[CCII TYPE III+ PIN SKT 24-16 ASSY](#)




TE Part #61276-2

[.058 DIA RECPT LP 24-20](#)



TE Part #374Z-03880

[Speed sen DSF 1210.00 SHV \(5m\)](#)



TE Part #04-1103-0008

[PT1MA-20-UP-420E-M6](#)

Documents

Product Drawings

[JACK DECOUPLER PCB RTANG](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_413524-5_AC.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_413524-5_AC.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_413524-5_AC.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[PCB Decoupled BNC Straight & Right Angle Jacks](#)

English

Product Specification

English