

323878 ✓ ACTIVE

SOLISTRAND

TE Internal #: 323878

Butt Splice, 16 – 14 AWG, 1.25 – 2 mm² Wire, Serrated, 2050 – 5180


CMA, Nickel, Orange, Length 13.44 mm [.529 in], Loose Piece,

Closed Barrel

[View on TE.com >](#)



Terminals & Splices > Splices



Splice Type: **Butt Splice**

Wire Size: **1.25 – 2 mm²**

Sealable: **No**

Splice Features: **Serrated**

Features

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Body Features

Product Weight	.832 g
Splice Features	Serrated
Primary Product Color	Orange

Dimensions

Outside Diameter	4.19 mm [.165 in]
Wire Size	2050 – 5180 CMA
Barrel Inside Diameter	2.16 mm [.085 in]
Terminal Material Thickness	.84 mm [.033 in]
Product Length	13.44 mm [.529 in]

Product Type Features

Splice Accessory Type	Splice
-----------------------	--------

Style Code	C
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Contact Base Material	Nickel
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46447
DAHT STRATO 22-10 ASSY

Customers Also Bought




TE Part #215079-6
MICRO-MATCH FOB.06P




TE Part #321884
TERM, STRAT, SOLIS, HT, 22-16, #4



TE Part #2-321801-3
SOLIS BUTT 22-16 COMM 22-18MIL




TE Part #2-1623746-5
ER74 2R2 5% AMMO PK



TE Part #323876
SOLIS BUTT HT 22-16COM22-18MIL



TE Part #1676914-4
YR1 0.1% 357R



TE Part #8-2176316-1
MELF SMA-A 22R 1% 50PPM 0207 1W



TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part #GAG15K4D609
[ESAP-ESA PROBE-3M,POLY TP WIRE](#)

Documents

Product Drawings

[SPLICE,SOLIS BUTT HT 16-14](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_323878_T.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_323878_T.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_323878_T.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[STRATO-THERM Terminals & Splices for High Temperature Applications](#)

English

Product Specifications

[Application Specification](#)

English