

350221-1

✓ ACTIVE


AMP-IN

TE Internal #: 350221-1

Receptacle, 28 – 26 AWG, .08 – .15 mm² Wire, Through Hole -
 Solder, Pre-Tin Plating, Package, Terminates To Wire & Cable, PCB
 Terminals

[View on TE.com >](#)

Terminals & Splices > PCB Terminals



PCB Terminal Type: Receptacle

Mating Pin Diameter: 2.36 mm [.093 in]

Compatible Insulation Diameter (Max): 1.45 mm [.057 in]

Compatible Insulation Diameter Range: .81 – 1.45 mm [.032 – .057 in]

Wire Size: 28 – 26 AWG

Features

Product Type Features

Terminal Features

Stud Hole

Usage Conditions

Insulation Option

Uninsulated

Operating Temperature Range

-55 – 105 °C [-67 – 221 °F]

Packaging Features

Packaging Quantity

7000

Packaging Method

Package

Dimensions

Terminal Material Thickness

.3 mm [.012 in]

Compatible Insulation Diameter (Max)

1.45 mm [.057 in]

Compatible Insulation Diameter Range

.81 – 1.45 mm [.032 – .057 in]

Wire Size

.08 – .15 mm²

Contact Features

PCB Terminal Type	Receptacle
Mating Pin Diameter	2.36 mm[.093 in]
Terminal Plating Material	Pre-Tin
Terminal Size	Miniature
Terminal Orientation	Straight

Termination Features

Termination Method to PCB	Through Hole - Solder
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 350015-1
093 PIN REC 22-18 0125PTPPHBZ

Customers Also Bought



TE Part #5555149-1
RCPT ASSY,LPF,RTANG,50 POSN



TE Part #103308-3
016 LOPRO HDR SP 15DP




TE Part #796634-3
3 POS 5.08MM R/A PLUG,TRM BLK



TE Part #796634-4
4 POS 5.08MM R/A PLUG,TRM BLK



TE Part #1-770966-0
02P MINI UMNL R/A HDR ASSY SN



TE Part #3-640108-1
AMP-IN, MINI 26-22 008PTLPHBZ




TE Part #796638-4
4POS 5.08MM CE R/A HDR,TRM BLK



TE Part #103308-7
034 LOPRO HDR SP 15DP



TE Part #1-1879135-5
RN 0603 147K 0.1% 10PPM 1K RL



TE Part #7-547605-1
JOY- STICK SELECTOR

Documents

Product Drawings

[093 PIN REC 28-26 PTTPHBZ](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_350221-1_N_c-350221-1-n.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_350221-1_N_c-350221-1-n.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_350221-1_N_c-350221-1-n.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English