



SPLICE

TE Internal #: 42329-1
Pigtail Splice / Thru Splice, 3200 – 3900 CMA, Steel, 0 Serration,
Length 3.81 mm [.15 in], Reel, Open Barrel, Solid / Stranded Wire,
SPLICE

[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: **Pigtail Splice, Thru Splice**
Sealable: **No**
Wire Size: **3200 – 3900 CMA**
Contact Base Material: **Steel**
Terminal Material Thickness: **.3 mm [.012 in]**

Features

Body Features

Product Weight	.089 g
----------------	--------

Packaging Features

Packaging Quantity	33000
Packaging Method	Reel

Product Type Features

Splice Type	Pigtail Splice, Thru Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	0
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

--	--



Contact Base Material	Steel
Barrel Type	Open

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	3200 – 3900 CMA
Terminal Material Thickness	.3 mm[.012 in]
Product Length	3.81 mm[.15 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 61021-1 SPLICE 18-16 AWG .0126 NPST	 TE Part # 42627-4 SPLICE 3232-8282 .0198 NPST	 TE Part # 7-2150684-7 OCEAN_2.0_SPARE_PART_KIT-100F	 TE Part # 2150684-2 OCEAN_2.0_Applicator-E-100F-REA
 TE Part # 61008-1 SPLICE 18-16 AWG .0158 TPST	 TE Part # 60933-2 SPLICE 2200-2900 .012 TPST	 TE Part # 41627-1 SPLICE 4000-10000 .025 ST	 TE Part # 2150684-1 OCEAN_2.0_Applicator-E-100F-REM
 TE Part # 160659-2 SPLICE 800-2500 .016 NPST			

Also in the Series | [SPLICE](#)




Crimp Wire Pins, Tabs & Ferrules(1)




Splices(63)


Customers Also Bought




TE Part #350629-5
.062 COMM P&S PIN AUNI/BR




TE Part #350628-5
.062 COMM P&S SOK AUNI/BR



TE Part #640254-1
KEYING PLUG .045 SQ PST CONN



TE Part #1703062-1
CAP, 2 CIRCUIT , UNIVERSAL MATE-N-LOK



TE Part #350415-5
.093 COMM P&S SOK 20-14 AUBR



TE Part #6-2378159-2
Power Versa-Lock PLUG, 1X2 KEY F



TE Part #8-2378159-2
Power Versa-Lock PLUG, 1X2 KEY H



TE Part #1-1703061-2
PLUG, 2 CIRCUIT , UNIVERSAL MATE-N-LOK



TE Part #794270-1
02P UMNL WIRE SEAL



TE Part #NB20384001
VERSAFIT-3/16-6-SP

Documents

Product Drawings

SPLICE 1200-2600 .012 NPST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42329-1_J_c-42329-1-j.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_42329-1_J_c-42329-1-j.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42329-1_J_c-42329-1-j.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English