



Connectors > RF Connectors > RF Modules > PCB RF Modules



Number of Coaxial Contacts: 10

PCB Mount Orientation: Right Angle

Body Material: Aluminum

Connector System: Cable-to-Cable

Number of Positions: 11

Features

Electrical Characteristics

Impedance	50 Ω
-----------	------

Operation/Application

Circuit Application	Signal
---------------------	--------

Contact Features

RF Connector Center Contact Material	Beryllium Copper
Contact Current Rating (Max)	1 A

Body Features

Body Plating Material	Trivalent Chromate
Body Material	Aluminum

Configuration Features

Number of Coaxial Contacts	10
PCB Mount Orientation	Right Angle
Number of Positions	11

Product Type Features

Connector System	Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

Mechanical Attachment



Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	25.4 mm[1 in]
--------------------	---------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2355002-1
MT Ferrule Kit, Plug, Without Pins, 12-F, MM



TE Part # 2313391-1
ASSEMBLY, HYBRID NanoRF/MT BP MODULE



TE Part # 2355002-2
MT Ferrule Kit, Plug, Without Pins, 24-F, MM



TE Part # 2378048-1
ASSY, NANORF/MT BP FULL; SOSA 14.26MM

Also in the Series | NanoRF Optical



PCB RF Modules(7)



RF Contacts(2)

Customers Also Bought



TE Part #1410188-3
MULTIGIG RT T2 7RW DC DF F-RGT



TE Part #1-1469492-9
MULTIGIG RT 9MM GUIDE/ESD UNKE



TE Part #2227303-1
CAGE ASSEMBLY, SFP, .140 SOLDE



TE Part #2302339-1
NanoRF SKT CONTACT, DAUGHTER CARD



TE Part #2302345-1
NanoRF PIN CONTACT, BACKPLANE



TE Part #1410187-3
MULTIGIG RT T2 7RW DC DF CT



TE Part #1410326-3
MULTIGIG RT T2 7RW DC DF CT



TE Part #1410946-2
MULTI-GIG SOC. CAP SCREW, CUSTOMIZED HDW



TE Part #2226881-1
CONNECTOR KIT, PLUG-IN MODULE, MT,V66.4



TE Part #2378048-1
ASSY, NANORF/MT BP FULL; SOSA 14.26MM



Documents

Product Drawings

ASSEMBLY, HYBRID NanoRF/MT DC MODULE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2359410-1_3.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2359410-1_3.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2359410-1_3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOSA Aligned Interconnect Solutions

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English